

#### 10282T-AK 14486T-AK 雨篷型随心雨花洒头

#### 安装之前

#### BEFORE YOU BEGIN

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。

Please leave these instructions for the consumer. They contain important information.

#### 注意事项：


1. 一定要先彻底冲洗供水管以清除管道中的杂质。
2. 推荐工作压力：2-5bars。
3. 花洒最高工作压力：0.5Mpa(5bar)。水压超过0.5Mpa(5bar)须安装减压阀。花洒最高工作温度及环境温度：60°C。请特别注意花洒须远离加热器，否则可能损坏花洒，甚至对使用者造成伤害。

#### NOTES:


1. Flush the water supply pipes thoroughly to remove debris.
2. Recommended working pressure: 2 to 5 bars.
3. The highest working pressure for showerhead is 0.5Mpa(5 bars). If it exceeds 0.5Mpa(5 bars), a pressure reducer is needed. The highest water and environment temperature is 60°C. Please keep showerhead away from heater, or maybe damage it and hurt user.

#### 安装尺寸

#### ROUGH-IN DIMENSIONS



10282T -AK




14486T-AK

#### 安装步骤

#### INSTALLATION

装花洒头(1)之前，先打开水源冲洗掉杂质。在花洒臂(2，客户自备)螺纹上缠绕足以密封的密封胶带或涂合适的密封胶，将花洒头旋到花洒臂上。



Flush both water supplies through the shower arm(2, not provided) for one minute before the showerhead(1) is installed. Apply tape or sealant to the exposed end of the shower arm. Tighten the showerhead with a strap wrench.

## 清洗说明

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可适用于科勒牌的水龙头及其配件上。


## CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.


Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

## 零件图

## SERVICE PARTS



**1149327\*\***  
**Showerhead**  
花洒头  
(仅用于10282T-AK)



**1149326\*\***  
**Showerhead**  
花洒头  
(仅用于14486T-AK)

\*\*订购时请说明颜色编号  
\*\*Color code must be specified when ordering