


Features

- 12" (30.5 cm) rough-in
- 2-1/8" (5.4 cm) glazed trapway
- Continuously heated water with 2 positionable spray wands
- Spray wands feature adjustable water pressure, temperature, oscillate and pulsate functions
- Air blower and heated seat with adjustable temperature settings
- Automatic deodorization and night light
- Remote control with two programmable presets
- Energy save function
- Anti-microbial materials used
- Quick-release design
- 11" (27.9 cm) x 8-1/2" (21.6 cm) water area
- 28-1/4" (71.8 cm) x 18-1/2" (47 cm) x 28" (71.1 cm)

COMFORT HEIGHT™ COMPACT TOILET WITH BIDET FUNCTIONALITY K-3608



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2
- Energy Policy Act of 1992
- ASME A112.4.2
- CSA B45.0
- CSA B45.1
- UL/cUL

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

Specified Model

| Model | Description | Trip Lever | Colors/Finishes | |
|--------------------------------|---|------------|-----------------------------|---|
| K-3608 | Compact one-piece elongated bowl toilet | left-hand | <input type="checkbox"/> 0 | <input type="checkbox"/> Other_____ |
| Recommended Accessories | | | | |
| K-7637 | 3/8" NPT angle supply with stop | | <input type="checkbox"/> CP | <input type="checkbox"/> PB <input type="checkbox"/> Other_____ |
| Optional Accessories | | | | |
| K-9483-L | Left-hand trip lever – non-CP | | <input type="checkbox"/> PB | <input type="checkbox"/> Other_____ |

Product Specification

The toilet shall be 28-1/4" (71.8 cm) in length, 18-1/2" (47 cm) in width and 28" (71.1 cm) in height. Toilet shall have a 12" (30.5 cm) rough-in. Toilet shall have a 11" (27.9 cm) x 8-1/2" (21.6 cm) water area. Toilet shall have 2-1/8" (5.4 cm) glazed trapway. Toilet shall feature continuously heated water with two positionable spray wands with adjustable water pressure, temperature, oscillate and pulsate functions Toilet shall have automatic deodorization and night light to illuminate the bowl. Toilet shall have a heated seat with adjustable temperature settings. Toilet shall have a remote control with two programmable user presets, an energy save function, anti-microbial materials that are used in the seat and nozzles and a quick-release design for ease of cleaning. Toilet shall be Kohler Model K-3608-_____-_____.

GABRIELLE™

Technical Information


| | |
|------------------------|-------------------------------------|
| Fixture: | |
| Configuration | one-piece, elongated |
| Water per flush | 1.6 gal (6 L) or 1.4 gal (5.3 L) |
| Passageway | 2-1/8" (5.4 cm) |
| Water area | 11" (27.9 cm) x 8-1/2" (21.6 cm) |
| Water depth from rim | 6" (15.2 cm) |
| Seat post hole centers | 5-1/2" (14 cm) |

Included components:

| | |
|-------------------------|---------|
| Seat | K-4744 |
| Tank cover | 85407 |
| Left-hand trip lever | 1068627 |
| Bolt cap accessory pack | 52048 |
| Tank accessory pack | 52265 |

Installation Notes

Install this product according to the installation guide.



Product Diagram