

COMFORT HEIGHT® TOILET K-3609

Features

- Vitreous china
- Elongated bowl
- 12" (305 mm) rough-in
- 1.28 gpf (4.8 lpf)
- Less seat and supply
- 2-1/8" (54 mm) glazed trapway
- AquaPiston® flushing system
- With Insuliner® insulated tank lining (-U)
- 10-1/2" (267 mm) x 7-1/8" (181 mm) water area
- 28-3/4" (730 mm) x 17-5/8" (447 mm) x 30-3/4" (781 mm)

ADA CSA B651 OBC



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ADA
- ICC/ANSI A117.1
- CSA B651
- OBC
- ASME A112.19.2/CSA B45.1
- EPA WaterSense®

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Trip Lever	Colors/Finishes
K-3609	Comfort Height toilet (shown)	left-hand	<input type="checkbox"/> 0 <input type="checkbox"/> Other_____
K-3609-RA	Comfort Height toilet	right-hand	<input type="checkbox"/> 0 <input type="checkbox"/> Other_____
K-3609-T	Comfort Height toilet - tank cover locks	left-hand	<input type="checkbox"/> 0 <input type="checkbox"/> Other_____
K-3609-TR	Comfort Height toilet - tank cover locks	right-hand	<input type="checkbox"/> 0 <input type="checkbox"/> Other_____
K-3609-U	Comfort Height toilet - Insuliner® tank	left-hand	<input type="checkbox"/> 0 <input type="checkbox"/> Other_____
K-3609-UR	Comfort Height toilet - Insuliner tank	right-hand	<input type="checkbox"/> 0 <input type="checkbox"/> Other_____

Recommended Accessories

K-4664	Brevia™ seat with cover	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-4650	Lustra™ elongated, open-front toilet seat – for Accessibility compliant installation	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-7637	Angle supply with stop - 3/8" NPT		<input type="checkbox"/> Other_____

Product Specification

The elongated bowl toilet shall be made of vitreous china. Toilet shall be 28-3/4" (730 mm) in length, 17-5/8" (447 mm) in width, and 30-3/4" (781 mm) in height with a 10-1/2" (267 mm) by 7-1/8" (181 mm) water area. Toilet shall be 12" (305 mm) rough-in and 2-1/8" (54 mm) glazed trapway. Toilet shall be 1.28 gpf (4.8 lpf) with AquaPiston flushing system. Toilet shall be less seat and supply. Toilet shall have optional Insuliner insulated tank lining (-U). Elongated bowl toilet shall be Kohler Model K-3609-_____ or K-3609-_____ -_____.

CIMARRON®

Technical Information

Fixture:	
Configuration	two-piece, elongated
Water per flush	1.28 gpf (4.8 lpf)
Passageway	2-1/8" (54 mm)
Water area	10-1/2" (267 mm) x 7-7/8" (200 mm)
Water depth from rim	6-3/8" (162 mm)
Seat post hole centers	5-1/2" (140 mm)

Included components:	
Bowl	K-4309
Tank cover	1086929
Tank cover with locks	1086929-T
Trip lever, left-hand	1059436
Trip lever, right-hand	1116014 (cont.)

(cont.) Bolt cap accessory pack	1013092
Tank accessory pack	1016548
Tank, left-hand trip lever	K-4421
Insuliner® tank, left-hand trip lever	K-4421-U

Installation Notes


Install this product according to the installation guide.

For back-to-back toilet installations: Use only a 45° double wye fitting.

Will comply with the Americans with Disabilities Act (ADA) when installed per the requirements of the 2010 ADA Standards of Accessible Design, Section 604 Water Closets, of the Act. The Model Plumbing Codes require the installation of elongated open-front toilet seats in public bathrooms.

Will comply with **CSA B651** when installed per Clause 4.3.6 of the standard.

Will comply with **OBC Barrier Free** requirements when installed per Clause 3.8.3.8 and 3.8.3.9.



Product Diagram