


2739T 800毫米墙出水滑动花洒支架



\*\*订购时请说明颜色编号  
\*\*Color code must be specified when ordering

2739T 800毫米墙出水滑动花洒支架

安装之前

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。

**注意事项：**  
一定要先彻底冲洗供水管以清除管道中的杂质

BEFORE YOU BEGIN


All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.


Please leave these instructions for the consumer. They contain important information.


**NOTES:**  
Flush the water supply pipes thoroughly to remove debris.

安装尺寸

ROUGH-IN DIMENSIONS



| 安装步骤                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        | INSTALLATION |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|
| <div>如何安装</div> <div><p>为使安装顺利，在墙面适当高度预装G1/2"内螺纹管道配件(5)。使用6mm六角扳手安装进水接头(6)。</p><p><b>注意：</b>管道配件不能突出或低于装修好的墙面不超过7mm，并垂直于装修好的墙面。</p><p>根据胀塞(1)直径，距离管道配件中心700-750mm钻孔。将胀塞塞入孔中。</p><p>从滑杆上取下支座(2)，从支座上取下上盖(4)。用自攻螺钉(3)连接支座。调整支座使内孔垂直，锁紧螺钉固定支座。</p><p>将滑杆装到进水接头(6)和支座上。用2.5mm六角扳手锁紧紧定螺钉(7)固定滑杆。</p><p>将上盖(4)装到支座上。</p><p>将皂盘(9)安装到皂盘托架(8)上。</p></div> <div></div> <div><p>To perform installation, install G1/2" female supply fitting(5) at the proper position on the finished wall. Install inlet connector(6) with 6mm hex wrench.</p><p><b>Note:</b> The supply fitting not extend or below the finished wall 7mm at most. It is vertical to the finished wall.</p><p>Drill holes according to diameter of the anchor(1), distance 700mm-750mm from the center of supply fitting. Press the anchor into the hole.</p><p>Take off the bracket(2) fromslide bar. Take off the upper cover(4) fromthe bracket. Connect the bracket(2) by the self-tapping screw(3). Adjust the bracket keeping the internal hole is vertical. Tighten the screw to secure the bracket.</p><p>Install the slide bar onto the inlet connector(6) and bracket. Secure the slide bar by tightening the crew(7). Tighten screw(7) by 2.5mm hex wrench.</p><p>Install the upper cover(4) onto the bracket.</p><p>Put the soap holder(9) onto the soap holder bracket(8).</p></div> |              |

| 安装后检查                                                                                                                          | INSTALLATION CHECKOUT                                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                 |
|--------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p>确定所有衔接螺母都已锁紧。开启主水源，检查是否有漏水。如有漏水，修理之。</p> <p>按住花洒托架的按钮上下滑动，可调节托架位置。</p>                                                      |                                                                                                                                                                                                                                                                                               | <p>Ensure that all coupling nuts are tightened. Turn on the main water supply, and check for leaks. Repair as needed.</p> <p>The height of hand shower holder can be adjusted by pressing the knob and sliding up and down.</p> |
| 清理说明                                                                                                                           | CLEANING INSTRUCTIONS                                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                 |
| <p>适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。</p> <p>有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。</p> | <p>All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc, which could adversely affect the finish and are not recommended for cleaning.</p> <p>Do not use abrasive cleaners or solvents on Kohler faucets and fittings.</p> |                                                                                                                                                                                                                                 |