



McAllister®

31-1/2" undermount double-bowl kitchen sink
11409

Features

- No faucet holes; requires wall- or counter-mount faucet
- 8" (203 mm) depth
- 3-3/4" (94 mm) drain opening
- Stainless steel with luster finish
- Large/small bowls
- Sink drain with strainer sold separately

Material

- Premium 18-gauge stainless steel

Installation

- Undermount
- Can be installed with or without reveal

Recommended Products/Accessories

- 7400 Stainless Steel Sink Drain and Strainer
- 11862 Sink Rack
- 11863 Sink Rack
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Included Components

- 91915 Hardware Kit



Codes/Standards

- ASME A112.19.3/CSA B45.4
- IAPMO Certification

STERLING® Stainless Steel Sinks Lifetime Limited Warranty


See website for detailed warranty information.

1-800-STERLING (1-800-783-7546)




Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

12-30-2024 22:29 - US/CA



Mounting bracket assembly provides a secure installation.



Technical Information

All product dimensions are nominal.

Basin configuration:	Large Bowl on Left
Bowl area (Left):	Length: 14-1/4" (362 mm) Width: 18-1/2" (470 mm) Bowl depth: 7-11/16" (195 mm) Water depth: 7-11/16" (195 mm)
Bowl area (Right):	Length: 14-1/4" (362 mm) Width: 15-3/4" (400 mm) Bowl depth: 7-11/16" (195 mm) Water depth: 7-11/16" (195 mm)
Drain hole:	3-3/4" (95 mm)
Template:	1315847-7, required, included

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.

Use the supplied cut-out template to select either a hidden or exposed rim.