




#### Features

- Vitreous china
- Elongated bowl
- Class Five® flushing system
- Polished chrome trip lever
- Less seat and supply
- 12" (305 mm) rough-in
- 1.28 gpf (4.8 lpf)
- 2-1/8" (54 mm) fully glazed trapway
- Optional Insuliner® tank and tank cover locks
- 11-1/4" (286 mm) x 8-1/4" (210 mm) water area
- 30" (762 mm) x 18" (457 mm) x 29-1/4" (743 mm)



#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- EPA WaterSense®

#### Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

#### Accessories

- 0: White
- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

#### Specified Model

| Model     | Description  | Trip Lever | Colors/Finishes            |                                     |
|-----------|--|------------|----------------------------|-------------------------------------|
| K-3998    | Class Five toilet (shown)                                | left-hand  | <input type="checkbox"/> 0 | <input type="checkbox"/> Other_____ |
| K-3998-RA | Class Five toilet  | right-hand | <input type="checkbox"/> 0 | <input type="checkbox"/> Other_____ |
| K-3998-RZ | Class Five toilet - Insuliner® tank and tank cover locks | right-hand | <input type="checkbox"/> 0 | <input type="checkbox"/> Other_____ |
| K-3998-T  | Class Five toilet - tank cover locks                     | left-hand  | <input type="checkbox"/> 0 | <input type="checkbox"/> Other_____ |
| K-3998-TR | Class Five toilet - tank cover locks                     | right-hand | <input type="checkbox"/> 0 | <input type="checkbox"/> Other_____ |
| K-3998-U  | Class Five toilet - Insuliner tank                       | left-hand  | <input type="checkbox"/> 0 | <input type="checkbox"/> Other_____ |
| K-3998-UR | Class Five toilet - Insuliner tank                       | right-hand | <input type="checkbox"/> 0 | <input type="checkbox"/> Other_____ |
| K-3998-UT | Class Five toilet - Insuliner tank and tank cover locks  | left-hand  | <input type="checkbox"/> 0 | <input type="checkbox"/> Other_____ |

#### Product Specification

The elongated bowl toilet shall be made of vitreous china. Toilet shall be 30" (762 mm) in length, 18" (457 mm) in width, and 29-1/4" (743 mm) in height with an 11-1/4" (286 mm) by 8-1/4" (210 mm) water area. Toilet shall be 1.28 gpf (4.8 lpf) with Class Five flushing system. Toilet shall include polished chrome trip lever. Toilet shall have 2-1/8" (54 mm) glazed trapway. Toilet shall be 12" (305 mm) rough-in. Toilet shall feature optional Insuliner tank and tank cover locks. Toilet shall be less seat and supply. Elongated toilet bowl shall be Kohler Model K-3998-\_\_\_\_ or K-3998-\_\_\_\_-\_\_\_\_\_.

# WELLWORTH®

## Recommended Accessories

|        |   |                             |                                     |
|--------|---|-----------------------------|-------------------------------------|
| K-4636 | Cachet® Quiet-Close™ seat with Quick-Release™ functionality | <input type="checkbox"/> 0  | <input type="checkbox"/> Other_____ |
| K-4688 | Cachet elongated toilet seat with cover                     | <input type="checkbox"/> 0  | <input type="checkbox"/> Other_____ |
| K-7637 | Angle supply with stop – 3/8" NPT                           | <input type="checkbox"/> CP | <input type="checkbox"/> Other_____ |

## Technical Information

|                        |                                       |
|------------------------|---------------------------------------|
| Fixture:               |                                       |
| Configuration          | two-piece, elongated                  |
| Water per flush        | 1.28 gpf (4.8 lpf)                    |
| Passageway             | 2-1/8" (54 mm)                        |
| Water area             | 11-1/4" (286 mm) x<br>8-1/4" (210 mm) |
| Water depth from rim   | 5-1/4" (133 mm)                       |
| Seat post hole centers | 5-1/2" (140 mm)                       |


### Included components:

|                         |         |
|-------------------------|---------|
| Bowl                    | K-4198  |
| Tank                    | K-4467  |
| Tank cover              | 1138565 |
| Trip lever              | K-9379  |
| Bolt cap accessory pack | 1013092 |

## Installation Notes

Install this product according to the installation guide.

**For back-to-back toilet installations:** Use only a 45° double wye fitting.



## Product Diagram