McAllister®

32" undermount double-bowl kitchen sink

11444

Features

- No faucet holes; requires wall- or counter-mount faucet
- 8-9/16" (217 mm) depth
- 3-5/8" (92 mm) drain opening
- Stainless steel with luster finish

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

7400 Stainless Steel Sink Drain and Strainer
11861 Sink Rack
K-23726 Drain treatment
K-23729 Stainless steel cleaner

Included Components

91915 Hardware Kit

Codes/Standards

ASME A112.19.3/CSA B45.4

STERLING® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.

STERLING
A KOHLER COMPANY

McAllister®

32" undermount double-bowl kitchen sink

11444



Mounting bracket assembly provides a secure installation.



Reveal



No Reveal





Technical Information

All product dimensions are nominal.

Basin configuration:	Equal Bowls
Min. base cabinet width:	36" (914 mm)
Bowl area (Left):	Length: 14-1/16" (357 mm) Width: 15-3/4" (400 mm) Bowl depth: 8-9/16" (218 mm) Water depth: 8-1/16" (205 mm)
Bowl area (Right):	Length: 14-1/16" (357 mm) Width: 15-3/4" (400 mm) Bowl depth: 8-9/16" (218 mm) Water depth: 8-9/16" (218 mm)
Drain hole:	3-5/8" (92 mm)
Template:	1315846-7, required, included

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.

Use the supplied cut-out template to select either a hidden or exposed rim.

Minimum base cabinet width: 33"-36" (33" cabinet may require cabinet modifications). Consult an installer for confirmation before proceeding.