



McAllister®

23-1/2" undermount single-bowl kitchen sink

11447

Features

- No faucet holes; requires wall- or counter-mount faucet
- 8" (203 mm) depth
- 3-3/4" (94 mm) drain opening
- Stainless steel with luster finish
- Rectangular bowl
- Single pack
- Sink drain with strainer sold separately

Material

- Premium 20-gauge stainless steel

Installation

- Undermount
- Can be installed with or without reveal

Recommended Products/Accessories

- 7400 Stainless Steel Sink Drain and Strainer
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Included Components

- 91915 Hardware Kit




Codes/Standards



- ASME A112.19.3/CSA B45.4
- IAPMO Certification

STERLING® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



Mounting bracket assembly provides a secure installation.



SilentShield™ Sound Pads

Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl
Min. base cabinet width: 27" (686 mm)

Bowl area (Only): Length: 20-7/8" (530 mm)
Width: 15-7/16" (392 mm)
Bowl depth: 8" (203 mm)
Water depth: 7-3/4" (197 mm)

Drain hole: 3-1/2" (89 mm)

Template: 1315840-7, required, included

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.