

Product Specification:


Model	K-1188T-C1	K-1189T-C1	K-1188T-RE	K-1189T-RE	More Info.
Features	Effervescence and chromatherapy		Effervescence		
Switch Position	At right	At left	At right	At left	
Dimensions	1905 x 1041 x 635mm				
Interior Dimensions	Rim: 1600 x 800mm Base: 1143 x 648mm				
Capacity to Overflow	537.5 Litres				
No. of Jets	11 effervescent ports				
Pump Access	Left	Right	Left	Right	
Weight	124.7 Kg				
Installation	Island, 3-wall alcove, drop-in, undermount				
Material	Gelcoat Fiberglass (FRP)				5.5
Electrical Service Requirements	2 Separate circuits required Protected with Class A GFCI orELCB				
Pump	4kW heater, 220-240 V, 50/60 Hz, 17 A (20 A service) 1.5 hp, 220-240 V, 50/60 Hz, 4 A (15 A service)				
Required Access Panel	Min:1016 (W) x 381 (H) mm				
Required					
Drain	K-7193				
Recommended					
Faucet	Faucet must reach a minimum of 200mm over the overflow channel into the bath and allow for a minimum 50mm air gap above the rim				Section 2
Laminar Faucet	K-8359 Laminar free-standing bath filler K-923 Laminar wall- or ceiling-mount bath filler K-924T Drip Tray				
Suite	The Purist Suite				
Note	Available in White (0) only				

Ground Fault circuit protection must be provided by installer.

*The above information are subject to change without notice.



Product Dimension:



K-1188T-C1/K-1189T-C1

*The above information are subject to change without notice.