


72740T 60厘米现代型滑动花洒支架



**订购时请说明颜色编号
**Color code must be specified when ordering

72740T 60厘米现代型滑动花洒支架

安装之前

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。


BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.

安装尺寸

ROUGH-IN DIMENSIONS



安装步骤



在墙面上选择一个合适的位置，用于安装滑动花洒支架。避开墙面内的电线和管道。

根据支架座(1,8)尺寸图，在墙面适当的高度打两个孔，将胀塞(2)分别塞入孔中。用螺钉(3)固定上支架座(1)于墙上。注意支架方向，有槽(10)的一端朝上。

试装支杆(4)、螺钉(5)和下支架座(8)，用笔标记下支架座的位置并找出两个孔的位置，钻两个孔，塞入胀塞(2)，用螺钉(3)固定下支架座于墙上。注意支架方向，有槽(10)的一端朝上。

将花洒挂架(9)穿过支杆(4)，并且调节花洒挂架转钮，使其位置合适。将下支架座盖(6)穿过支杆，开口方向朝下。用螺钉(5)将支架组件固定在支架座(1,8)上。

分别将上下支架座盖(6)装在支架座(1,8)上，再扣上支杆盖(7)。



INSTALLATION

Decide on a suitable position for the slide bar avoiding buried cables and pipes in the wall.

Drill two holes at the proper height in the wall as the bracket(1,8) dimensions. Put anchors(2) into the holes. Install the bracket(1) with screws(3) in the wall. Ensure the groove(10) of the bracket upward.

Rehearse the slide bar(4), screws(5) and bracket(8). Mark the outline of the bracket with a pencil on the wall, and find the position of the holes. Drill two holes and put anchors(2) into the holes. Install the bracket with screws(3) in the wall. Ensure the groove(10) of the bracket upward.

Slide the handshower holder(9) onto the bar(4). Adjust the holder to the proper position. Slide the lower bracket cover(6) onto the slide bar with the opening facing downwards. Tighten the slide bar kit onto the brackets(1,8) with screws(5).

Slide the bracket covers(6) onto the brackets(1,8), and then install the covers(7).

清洗说明

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可适用于科勒牌的水龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc, which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

质量担保

科勒担保，在原购客户拥有其安装科勒龙头的住所的期限内，科勒龙头不存在由阀芯造成的龙头滴漏现象，PVD部件在正常家用的情况下无材料及制造工艺上的瑕疵。如龙头在正常家用情况下出现滴漏，如龙头在正常家用情况下出现滴漏，科勒将为客户更换新的阀芯，令其恢复正常状态。

龙头的其他部分或配件在正常家用的情况下自购买之日起五年内无材料及制造工艺上的瑕疵。如产品被用于商业目的，则科勒担保该产品自购买之日起一年内无材料及制造工艺上的瑕疵。

本担保仅适用于原购客户。担保范围不包括：环境温度低于0°C水中的杂质过多、水质过硬的情况。

未提及事项及担保条款全部参照官网信息 www.kohler.com.cn/support/customer-service-guarantee

各产品购买地区/国家科勒担保服务中心

地区/国家 地址

中国大陆 科勒(中国)投资有限公司
中央客户服务中心
中国上海市静安区江场三路158号
邮编：200436
免费咨询保修电话：+ (86) 800-820-2628
+ (86) 400-820-2628
网址：<http://www.kohler.com.cn>

中国台湾、中国香港和中国澳门 科勒亚洲有限公司
中国香港湾仔区湾仔告士打道88号14楼
电话：+ (852) 3125 7728
传真：+ (852) 2802 2162

Kohler Service Centers in Asia Pacific

Refer to the website for specific product warranty details: kohlerasiapacific.com

WARRANTY

Kohler warrants this faucet to be leak and drip free, and the PVD (Physical Vapor Deposition) component of this product to be free of defects in material and workmanship during normal residential use for as long as the original consumer purchaser owns his or her home. If the faucet should leak or drip during normal use, Kohler will, free of charge, mail to the purchaser the cartridge necessary to put the faucet in good working condition.

All other aspects of the faucet or accessories ("Faucet") for five years to be free of defects in material and workmanship during normal residential use from the date of purchase. If the Faucet is used commercially, Kohler warrants the Faucet to be free from defects in material and workmanship for one (1) year from the date the product is purchased.

This warranty is applied for original consumer. This warranty does not cover problems arising from environment temperature below 0°C, excessive water impurities, hard water quality.

Please refer to the KOHLER website for all unmentioned matters and guarantee terms www.kohler.com.cn/support/customer-service-guarantee

Kohler Warranty Obligor/Service Center for Region or Country of Purchase

Region/Country Address

China mainland Kohler China Investment Co., Ltd.
Central Customer Service Centre
NO.158 Jiang Chang San Road,
Jing'an District, Shanghai, PRC
Post Code: 200436
Toll-Free Service Call:
+ (86) 800-820-2628
+ (86) 400-820-2628
Website: <http://www.kohler.com.cn>

Taiwan, Hong Kong and Macau, China Kohler Asia Pacific Limited
14/F, No. 88 Gloucester Road,
Wan Chai, Hong Kong, PRC
Tel: + (852) 3125 7728
Fax: + (852) 2802 2162