

98951T-L Multi-function Katalyst Handshower
98952T-L Multi-function Katalyst Handshower-Traditional

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.


NOTES:

1. Flush the water supply pipes thoroughly to remove debris.
2. The highest working pressure for spray is 0.5MPa(5 bar). If it exceeds 0.5MPa(5 bar), a pressure reducer is needed. The highest water and environment temperature is 60°C. Please keep handshower, shower head and the shower arm away from heater, or it may become damaged and cause injury to the user.

STANDARD APPLICABLE

Special model meets or exceeds the following at date of manufacture: TIS


ROUGH-IN DIMENSIONS



INSTALLATION

Put the washer(1) into the shower hose(2, not provided) connector, screw the handshower(3) to the shower hose. Connect another end of shower hose to the water supply.

NOTE: The limiter(4) is used when water pressure is too high. Unscrew the handshower, put the limiter into the handshower inlet. Put the washer into the hose connector. Connect the handshower and hose.




CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc, which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

SERVICE PARTS



**Color code must be specified when ordering