

Features

- Solid metal construction
- Flexible G1/2" supply hose
- Leak-free ceramic disk valve
- Coin aerator (easy install & easy clean)
- 99 mm spout reach
- Lift and turn handle operation
- Flow rate reduced by 30% - meets LEED guidelines for reduction in water consumption.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2067-2552


Installation Notes

Install this product according to the installation guide.

Specified Model

Model	Description	Color/Finished
K-98827T-4CD	Kumin cold water single-hole single-control lavatory faucet	CP: Polished Chrome

COLD WATER SINGLE-HOLE SINGLE-CONTROL LAVATORY FAUCET K-98827T




Flow Curve

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



Product Diagram

คุณลักษณะ

- ผลิตจากโลหะ
- สายน้ำดีขนาด G1/2"
- พร้อมเซรามิกวาล์วกันการรั่วซึม
- ปากก๊อกแบบเปิดง่าย
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 99 มม.
- โยกและหมุนเพื่อใช้งาน
- ลดอัตราการใช้น้ำลง 30% ตามข้อกำหนดของ LEED

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2067-2552

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกเดี่ยวอ่างล้างหน้าแบบก้านโยก K-98827T



รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-98827T-4CD	ก๊อกเดี่ยวอ่างล้างหน้าแบบก้านโยก รุ่นคูมิน	CP: สีโครมเงา




กราฟแสดงอัตราการไหล

หมายเหตุ: อัตราการใช้ไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 psi)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์