

# KOHLER®

## 星都 URBANITY

安装说明书

INSTALLATION INSTRUCTIONS

开放式挂柜

OPEN SHELF

K-99916T-LK/K-99917T-LK


### ROUGHING-IN

### 尺寸图


Reference Value  
参考值

**K-99916T-LK**  
星都开放式横柜

UNIT : mm  
单位: 毫米



**K-99917T-LK**  
星都开放式竖柜



科勒公司保留随时变更图中标示尺寸的权利，无需另行通知。  
Kohler reserves the right to change marked dimensions without prior notice.

中山科勒卫浴有限公司  
广东省中山市中山火炬开发区兴业路13-1号

邮编：528437

## INSTALLATION


## 安装

### K-99916T-LK

- Drill two  $\Phi 6$  mounting holes on the wall with horizontal distance of 888mm.
- Insert anchors into the holes and fix with screws.  
**Note:** Do not tighten the screws. About 5mm of the screws shall be left outside the wall to hang the shelf.
- Hang the shelf onto wall by aligning the mounting holes on its bottom with the screws.

### K-99916T-LK

- 在墙上钻2个 $\Phi 6$ 的安装孔，水平孔距为886mm。
- 将入墙胶粒敲入安装孔内，并拧入安装螺钉。  
注：安装螺钉不要拧到底，需外露约5mm，用于挂柜体。
- 将柜体底部的安装孔对准已固定在墙上的安装螺钉，将柜体挂在安装螺钉上。



### K-99917T-LK

- Drill two  $\Phi 6$  mounting holes on the wall with horizontal distance of 198mm.
- Insert anchors into the holes and fix with screws.  
**Note:** Do not tighten the screws. About 5mm of the screws shall be left outside the wall to hang the shelf.
- Hang the shelf onto wall by aligning the mounting holes on its bottom with the screws.

### K-99917T-LK

- 在墙上钻2个 $\Phi 6$ 的安装孔，水平孔距为198mm。
- 将入墙胶粒敲入安装孔内，并拧入安装螺钉。  
注：安装螺钉不要拧到底，需外露约5mm，用于挂柜体。
- 将柜体底部的安装孔对准已固定在墙上的安装螺钉，将柜体挂在安装螺钉上。

