





**订购时请说明颜色编号
**Color code must be specified when ordering

562T-B4 下抽拉厨房龙头	
安装之前	BEFORE YOU BEGIN
所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。 说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。 注意事项： - 一定要先彻底冲洗供水管以清除管道中的杂质。 - 如果是安装新洗涤盆，可将水龙头先装到洗涤盆上。 - 花洒最高工作压力：0.5MPa(5bar)。水压超过0.5MPa(5bar)时必须安装减压阀。花洒最高工作温度及环境温度：60°C。请特别注意花洒同花洒连接的臂管须远离加热器，否则可能损坏花洒及其密封件，甚至对使用者造成伤害。 - 水嘴加施的水效标识表明本产品的水效等级等性能符合GB25501-2019《水嘴水效限定值及水效等级》的要求，是产品符合性的一种标识。	All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice. Please leave these instructions for the consumer. They contain important information. NOTES: - Flush the water supply pipes thoroughly to remove debris. - For new installations, install the faucet to sink before installing. - The highest working pressure for sprayhead is 0.5MPa (5bar). If it exceeds 0.5MPa(5bar), a pressure reducer is needed. The highest water and environment temperature is 60°C. Please keep sprayhead away from heater, or it may become damaged and cause injury to the user. - The water efficiency label applied to the faucet indicates that the water efficiency grade and other performance of the product meet the requirements of GB 25501-2019 "Minimum Allowable Values of Water Efficiency and Water Efficiency Grades for Faucets" which is a marking of product conformity.
安装尺寸	ROUGH-IN DIMENSIONS

安装步骤


INSTALLATION



安装垫圈(1)，有泡沫的面朝下。安装水龙头，把手置于右边。

将螺钉(2)旋进安装环(3)，直到螺钉露出安装环6mm。



将垫片(4)安装到牙管(5)上，安装环旋到牙管上。



Install the gasket(1), foam side down. Install the faucet, the handle is located on the right side.

Partially thread the screws(2) into the ring(3) until they extend 6mm out the opposite side.


Slide the washers(4) onto the shank(5) and thread the ring onto the shank.



调整安装环上螺钉的位置并拧紧。

连接并锁紧软管(6)到水源上。贴“COLD”签(7)的软管连接冷水。



打开冷热水源，让水流出约一分钟。



Position the screws on the ring onto the shank. Tighten the screws.

Connect and tighten the supply hoses(6). The hose with “COLD” label(7) should be connected to cold water.


Turn on the water supplies. Flush the hot and cold for about one minute.



将重锤(9)松松的安装在花洒软管(8)上。

转动卡扣上的旋钮，连接花洒软管到龙头接管上。



如图所示，调整重锤到合适位置并锁紧固定。



Loosely attach the weight(9) to the spray hose(8).


Turn the knob of the tab, align and connect the spray hose.

Position the weight as shown and tighten securely.




检查花洒抽拉是否顺畅。

如果需要，调整重锤到适当的位置。



Check for smooth operation.


Adjust the weight as needed for proper positioning and operation.



龙头维护：

打开龙头，揉搓喷嘴以清除杂质。

当有杂质使水流变小时，取下花洒头，清洗滤网垫片。重新装回即可。



Faucet Maintenance:

With the water running, rub the nozzles to dislodge debris.

To improve the flow, disconnect the sprayhead and clean the screen washer. Reassemble.

安装结果检查

检查并确保所有衔接处都已拧紧，确保手柄在关的位置。打开主水源和排水系统，检查并修理有漏水的接口。

INSTALLATION CHECKOUT

Ensure that all coupling nuts are tight. Ensure that the lever handle is in the off position. Turn on the main water supply and drain, and check for leaks. Repair as needed.

清洗说明

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

龙头本体背面标有“LEAD FREE”字样，即产品符合美国AB1953法令的要求。

"LEAD FREE" is marked on the back of the faucet signifying its compliance with the United States AB1953.