

KALLISTA®

Per Se® Sink Faucet, Tall Spout

P24736

FEATURES

- Solid metal construction for durability and reliability
- Two-handle, widespread lavatory faucet for 8" (203 mm) - 16" (406 mm) centers
- Quarter-turn washerless ceramic disc valves
- 1.2 gal/min (4.5 l/min) maximum flow rate
- Includes Soft Touch drain
- Thin, slender form
- Meets CalGreen requirements for bathroom sink faucets
- Complements the Per Se collection


CODES/STANDARDS APPLICABLE

Specified model meets or exceeds the following:

- ASME A112.18.1/CSA B125.1
- ICC/ANSI A117.1
- ADA*
- CSA B651*
- OBC*
- NSF 61

ADA **CSA B651** **OBC**

*Compliant when installed to the specific requirement of this regulation



Soft Touch Drain

INSTALLATION NOTES		
Mounting surface hole size. All dimensions are nominal.		
Spout	Ø 5/8" (16 mm)	
Handles	Ø 1-5/16" (33 mm)	
Deck Thickness	Min	Max
Spout	--	2-1/2" (64 mm)
Handles	--	1-5/8" (41 mm)

SPECIFIED MODEL		
Model	Description	Finishes
P24736-LV	Per Se Sink Faucet, Tall Spout, Lever Handles	<input type="checkbox"/> CP Polished Chrome <input type="checkbox"/> AD Nickel Silver <input type="checkbox"/> AG Brushed Nickel <input type="checkbox"/> AF French Gold

We reserve the right to make revisions without notice in the design of products or in packaging unless this right has specifically been waived at the time the order is accepted.