

Features

- Brass construction.
- Leak-free 1/4 ceramic disc valve with lifetime warranty.
- Durable KOHLER finishes resist corrosion and tarnishing.
- Directionally adjustable, laminar-flow aerater.
- Includes pop-up drain.
- 151 mm spout reach.
- Lever handle.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2067-2552
- EN 817-2008
- GB 18145-2014
- EN 200-2008

Installation Notes

Install this product according to the installation guide.


WIDESPREAD LAVATORY FAUCET K-73060X-4/K-73060T-4 K-73060T-3



Specified Model


Model	Description	Color/Finishes	
K-73060X-4 K-73060T-4	Composed widespread lavatory faucet (lever handles)	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-73060T-3	Composed widespread lavatory faucet (Cross handles)	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others

For a full range of color finishes in your market, please contact your local Kohler representative.





Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



K-73060X-4 / K-73060T-4



K-73060T-3

Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- เซรามิกวาล์วป้องกันการรั่วซึมแบบหมุน 90 องศา รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษของโคห์เลอร์ คงทน เงางาม
- ปากก๊อกปรับทิศทางได้ สายน้ำสัมผัสอ่อนนุ่ม
- พร้อมสະดืออ่างแบบป๊อปอัพ
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 151 มม.
- มือบิดแบบก้านโยก

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2067-2552
- EN 817-2008
- GB 18145-2014
- EN 200-2008

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกผสมอ่างล้างหน้าเซ็นเตอร์ 8"

K-73060X-4/K-73060T-4


K-73060T-3



รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-73060X-4 K-73060T-4	ก๊อกผสมอ่างล้างหน้าเซ็นเตอร์ 8" มือบิดแบบก้านโยก รุ่นคอมโพส	<input type="checkbox"/> CP: สีโครมเงา	<input type="checkbox"/> อื่นๆ
K-73060T-3	ก๊อกผสมอ่างล้างหน้าเซ็นเตอร์ 8" มือบิดแบบครอส รุ่นคอมโพส	<input type="checkbox"/> CP: สีโครมเงา	<input type="checkbox"/> อื่นๆ


ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน





กราฟแสดงอัตราการไหล

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.



K-73060X-4 / K-73060T-4



K-73060T-3

หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์