

EXPOSED WALL-MOUNT BATH SHOWER MIXER K-97369T

Features

- Brass construction
- Leak-free ceramic disc valve with lifetime warranty
- Durable Kohler finishes resist corrosion and tarnishing
- Directionally adjustable, laminar-flow aerator
- High-temperature limit stop for added safety
- Katalyst air-induction technology for powerful and even coverage
- Includes 130 mm Rain Duet push button, 3-function handshower
- Line-matched faucets and accessories available

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552
- GB 18145-2014
- EN 817-2008

Installation Notes


Install this product according to the installation guide.




Specified Model

Model	Description	Color/Finished
K-97369T-4	Avid exposed wall-mount bath shower mixer	☐ CP: Polished Chrome ☐ TT: Titanium

For a full range of color finishes in your market please contact your local Kohler representative



Flow Curve – Bath Spout




Flow Curve – Handshower

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- พร้อมเขวามีการวัดกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษจากโคโธเลอรัค คงทน เงามาม
- ปากก๊อปปรีทิตทางได้ สายน้ำส้มผัสอ่อนนุ่ม
- ระบบควบคุมอุณหภูมิ เพื่อเพิ่มความปลอดภัย
- หัวฝักบัวระบบแคตตาลิส เทคโนโลยีการอัดอากาศ เพื่อสายน้ำชุ่มฉ่ำเต็มสัมผัส
- พร้อมหัวฝักบัวเรนดู้อิตขนาด 130 มม. ปุ่มกดปรับสายน้ำได้ 3 ระดับ
- มีก๊อปปรีทิตและอุปกรณ์ประกอบห้องน้ำเข้าชุดกับผลิตภัณฑ์

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มาตรฐาน 2066-2552
- EN 817-2008
- GB 18145-2014


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


รุ่นผลิตภัณท์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-97369T-4	ก๊อกลดแสงสว่างและยับยั้งการเติบโตของเชื้อรา	☐ CP: สีโครมเงา	☐ TT: โททาเนียม

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศไทยของท่าน



กราฟแสดงอัตราการไหล ก้อนกลางอ่าง




กราฟแสดงอัตราการไหล ผักบัวสายอ่อน

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์