


74036T-4 挂墙式浴缸花洒龙头
74035T-4 挂墙式花洒龙头
73195T-4 挂墙式花洒龙头(不含花洒)



74036T-4 挂墙式浴缸花洒龙头
74035T-4 挂墙式花洒龙头
73195T-4 挂墙式花洒龙头(不含花洒)

安装之前

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。

注意事项:

1. 一定要先彻底冲洗供水管以清除管道中的杂质。
2. 检查供水管有无损坏和漏水。如需要, 进行替换和维修。
3. 遵守当地管路安装条例。
4. 切换器正常工作的最小压力为0.05MPa(0.5bar)。
5. 花洒最高工作压力: 0.5MPa(5bar)。水压超过0.5MPa(5bar)时必须安装减压阀。花洒最高工作温度及环境温度: 60°C。请特别注意花洒同花洒连接的臂管须远离浴霸, 否则可能损坏花洒及其密封件, 甚至对使用者造成伤害。

安装尺寸


BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice. Please leave these instructions for the consumer. They contain important information.


NOTES:

1. Flush the water supply pipes thoroughly to remove debris.
2. Inspect the supply tubing for damage and leakage. Replace and maintain as necessary.
3. Observe local plumbing codes.
4. The minimum inlet water pressure for the diverter is 0.05MPa(0.5bar).
5. The highest working pressure for handshower is 0.5MPa(5bar). If it exceeds 0.5MPa(5bar), a pressure reducer is needed. The highest water and environment temperature is 60°C. Please keep the handshower, showerhead and shower arm away from heater, or it may become damaged and cause injury to the user.

ROUGH-IN DIMENSIONS



淋浴器加施的水效标识表明本产品的水效等级等性能符合GB 28378-2019《淋浴器水效限定值及水效等级》的要求，是产品符合性的一种标识。




安装步骤

如何安装水龙头

在两个接头(1)涂上螺纹密封膏或缠绕密封胶带，然后旋入冷热供水管中。

调节两个接头，使其中心距离为150mm并保持同一水平。凸出墙面的尺寸应该在29mm。将装饰罩(2)旋入接头，紧贴装修后的墙壁。

将垫片(3)放入螺母(4)中，把螺母旋到接头(1)上，用带状扳手锁紧。



INSTALLATION

How to Install the Faucet

Use appropriate thread sealants or thread tape on offset connectors(1). Install the two offset connectors into the hot and cold supply pipes.


Adjust the center-to-center distance between the connectors to 150mm horizontally. They should extend 29mm beyond the finished wall. Thread the escutcheons(2) onto the connectors until they contact the finished wall.

Put the washers(3) into the nuts(4). Thread the nuts onto the connectors(1) and tighten by wrench.

如何安装花洒

先去掉出水口接头保护套。

将垫片(5)装入到软管(6)的A端，然后与出水口接头(7)连接。将垫片(8)装入到软管的B端，根据需要将限流器(9)装入花洒(10)进水口，然后将B端与花洒连接。



How to Install the Handshower


Remove the guard on the outlet connector firstly.

Put the washer(5) into end A of the hose(6), and then connect to the faucet outlet(7). Put the washer(8) into end B of the hose, and install the regulator(9) into the handshower(10) inlet if needed, then connect end B of the hose to the handshower inlet.

如何安装托架

在墙面选一合适的位置来安装托架。根据孔距在墙面上标记钻孔的位置，依据胀塞(11)直径打孔，安装胀塞。

旋紧螺钉(12)，使底座(13，平面朝上)固定并紧贴墙壁。将托架(14)扣在底座上，使凸台嵌入豁口。



How to Install the Bracket

Determine a suitable location on the finished wall to install the bracket. Mark bracket base mounting hole locations on the wall according to the dimension. Drill two holes on the finished wall, the holes should match the anchors(11). Install the anchors.

Tighten screws(12) to secure bracket base (13, flat side upward). Put the bracket (14) onto the bracket base and lock by stopper.

安装结果检查

检查并确保所有的衔接处都已拧紧。确保手柄在关的位置。

打开排水系统和主要供水源，检查并修理有漏水的接口。


74036T-4: 挂墙式浴缸花洒龙头

取下花洒(10)，用硬币取下起泡器(16)。打开冷热水让水流约一分钟，以清除杂质。检查渗漏并清洗起泡器。

将切换器(15)轻轻提起，顺时针旋转切换器，让水流约一分钟，以清除杂质并检查渗漏。关闭龙头，装回花洒和起泡器。

74035T-4/73195T-4: 挂墙式花洒龙头

对于74035T-4，先取下花洒(10)。打开冷热水，让水流约一分钟，以清除杂质。检查渗漏。关闭水龙头。对于74035T-4，装回花洒。



Ensure that all coupling nuts are tightened. Ensure that the handle is in the off position.

Turn on the main water supply, and check for leaks. Repair as needed.

74036T-4: Wall Mount Bath Shower Faucet

Remove the handshower(10), remove the aerator(16) by coin. Run hot and cold water through the faucet for about one minute to remove any debris. Check for leaks. Remove any debris from the aerator.

Lift the diverter(15) gently, turn clockwise for shower. Run hot and cold water through the faucet for about one minute to remove any debris. Check for leaks. Shut off the faucet, reinstall the handshower and aerator .

74035T-4/73195T-4: Wall Mount Shower Faucet

For 74035T-4, remove the handshower(10). Run hot and cold water through the faucet for about one minute to remove any debris. Check for leaks. Shut off the faucet. For 74035T-4, reinstall the handshower.

使用说明

轻轻打开把手，顺时针旋转把手为热水，逆时针旋转把手为冷水。龙头切换器处于正常位置时出水口出水；将切换器轻轻提起，顺时针旋转切换器，花洒出水；关闭龙头，逆时针旋转切换器到停止位置。

HANDLE OPERATION

Lift handle gently. Turn clockwise for hot water, turn counter-clockwise for cold water. Water flows out from spout when faucet diverter is in the normal position. Lift the diverter gently, turn clockwise for handshower. Shut off the faucet, turn counter-clockwise until it stops.

清洗说明

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可使用时科勒牌的水龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.