

KALLISTA®

Counterpoint® Sink Faucet

FEATURES

- Solid brass construction for durability and reliability
- Two-handle, widespread sink faucet for 8" (203 mm) - 16" (406 mm) centers
- 1.2 gal/min (4.5 l/min) maximum flow rate
- Quarter-turn washerless ceramic disc valves
- Meets CalGreen requirements for bathroom sink faucets
- Complements the Counterpoint collection

CODES/STANDARDS APPLICABLE

Specified model meets or exceeds the following:


- ASME A112.18.1/CSA B125.1
- NSF 61
- ADA*
- ICC/ANSI A117.1
- EPA WaterSense®
- CSA B651*
- OBC*
- All applicable US Federal and State material regulations

ADA CSA B651 OBC



*Compliant when installed to the specific requirement of this regulation

P23202



INSTALLATION NOTES

Mounting Surface Hole Size. All dimensions are nominal.		
Spout	Ø 1" (26 mm)	
Handles	Ø 1-5/16" (32 mm)	
Deck Thickness	Min	Max
Spout	—	2-1/2" (64 mm)
Handles	—	1-1/2" (38 mm)

SPECIFIED MODEL

Model	Description	Finishes		
P23202-LV	Counterpoint Sink Faucet, Metal Lever Handles	<input type="checkbox"/> CP Polished Chrome	<input type="checkbox"/> AD Nickel Silver	<input type="checkbox"/> AG Brushed Nickel
P23202-SL	Counterpoint Sink Faucet, Stone Lever Handles	<input type="checkbox"/> CP Polished Chrome	<input type="checkbox"/> AD Nickel Silver	<input type="checkbox"/> AG Brushed Nickel

We reserve the right to make revisions without notice in the design of products or in packaging unless this right has specifically been waived at the time the order is accepted.