

Features

- Brass construction
- Leak-free ceramic disc valve with lifetime warranty
- Durable Kohler finishes resist corrosion and tarnishing
- Flexible G1/2" supply hoses for easy installation
- Metal mounting hardware assures a secure installation
- Lever handle
- 178 mm spout reach

COLD ONLY KITCHEN FAUCET K-21370T-4CD



Codes/Standards Applicable

- Specified model meets or exceeds the following:
- TIS 2067-2552


Installation Notes

Install this product according to the installation guide.

Specified Model

Model	Description	Color/Finished
K-21370T-4CD	Taut cold only kitchen faucet	CP: Polished Chrome


For a full range of color finishes in your market please contact your local Kohler representative.



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

