KOHLER®

1355515-IN2

Record your model number: _____

WARNING: Risk of scalding. High water temperature can cause severe burns. Set the valve water temperature at or below 140°F (60°C). Refer to the temperature adjustment instructions for the valve.

CAUTION: Risk of product damage and personal injury. Keep the product away from a heater.

NOTE: The maximum operating pressure for this product is 0.5 MPa (5 bar). If the pressure exceeds 0.5 MPa (5 bar), install a pressure reducer.

Follow all local plumbing and building codes.

Turn OFF the water supply.

The product shown may differ from your actual product. The installation steps still apply.

READ AND FOLLOW ALL INSTRUCTIONS

SAVE THESE INSTRUCTIONS

1A. Flush debris before installing the hose.

2A. If required, install the flow restrictor.

4A. Maintenance: Periodically rub debris from the nozzles while water is running.

5A. Maintenance: Periodically rinse debris from the screen washer.

Square-head handshower operation:

6A. Katalyst spray

6B. Massage spray

6C. Champaign spray

Round-head handshower operation:


7A. Katalyst spray

7B. Massage spray

7C. Komotion spray


Need help? Contact our Customer Care Center.

- Email: indiacustomercare@kohler.com
- Call: 1800-103-2244
- **Care and cleaning:** Please refer to the Care and Cleaning on the product detail page.




This product is covered under the **KOHLER® India Warranty Policy**, found at kohler.co.in/warranty. For a hardcopy of warranty terms, contact the Customer Care Center.


5



6



7



©2026 Kohler Co.