

Composed Hinged Door Enclosure

Product Description: Composed Hinge Door Enclosure

Colour/Finish: Chrome

Material: Coated Safety Glass & Aluminium

Product Weight (kg):

Part Number	Gross Weight (Kg)
1.1922.007	37.04
1.1922.008	42.43
1.1922.009	46.43
1.1922.010	55.65
C1.1922.011	64.00*
1.1922.012	31.97
1.1922.013	33.46
1.1922.014	37.67



Optional Items:

Part Number	Part Description
1.1826.277	10 mm Filler Profile
1.1826.278	18 mm Filler Profile


Guarantee (Years): 5

Additional Information: 8 mm thick safety glass.
20 mm adjustment for out of true walls.

Reversible for left or right fixing. Panel A and C are fixed, while Door B is hinged.

Dimensions (mm):

Part Number	Product Size	A (mm)	B (mm)	C (mm)	Door Opening (mm)
1.1922.007	800 mm	300	500	-	490
1.1922.008	900 mm	350	550	-	540
1.1922.009	1000 mm	350	650	-	640
1.1922.010	1200 mm	550	650	-	640
C1.1922.011	1400 mm	750	650	-	640
1.1922.012	760 mm	-	-	760	-
1.1922.013	800 mm	-	-	800	-
1.1922.014	900 mm	-	-	900	-



* Product supplied in 2 boxes.

Kohler UK
Sales and Technical:
0800 001 4466
info@kohler.co.uk
www.KOHLER.co.uk

THE BOLD LOOK
OF **KOHLER**®