

Composed Sliding Door Enclosure

Product Description: Composed Sliding Door Enclosure

Colour/Finish: Chrome

Material: Coated Safety Glass & Aluminium

Product Weight (kg):

Part Number	Gross Weight (Kg)
1.1922.015	49.35
1.1922.016	54.29
C1.1922.018	63.97*
C1.1922.019	68.01*
C1.1922.021	76.31*
C1.1922.022	77.33*
1.1922.023	30.89
1.1922.024	32.37
1.1922.025	36.42

Optional Items:

Part Number	Part Description
1.1826.277	10 mm Filler Profile
1.1826.278	18 mm Filler Profile

Guarantee (Years): 5

Additional Information: 8 mm thick safety glass.
20 mm adjustment for out of true walls.




Part Number	Part Description
1.1922.023	Side Panel 760mm
1.1922.024	Side Panel 800mm
1.1922.025	Side Panel 900mm

Reversible for left or right fixing.
Panel A and C are fixed, while Door B slides.

Dimensions (mm):

Part Number	Product Size	A (mm)	B (mm)	C (mm)	Door Opening (mm)
1.1922.015	1100 mm	500	600	-	427
1.1922.016	1200 mm	550	650	-	477
C1.1922.018	1400 mm	650	750	-	577
C1.1922.019	1500 mm	750	750	-	577
C1.1922.021	1600 mm	750	850	-	677
C1.1922.022	1700 mm	850	850	-	677
1.1922.023	760 mm	-	-	760	-
1.1922.024	800 mm	-	-	800	-
1.1922.025	900 mm	-	-	900	-



* Product supplied in 2 boxes.

Kohler UK
Sales and Technical:
0800 001 4466
info@kohler.co.uk
www.KOHLER.co.uk

THE BOLD LOOK
OF **KOHLER**®