

Features

- Brass construction
- Durable Kohler finishes resist corrosion and tarnishing
- Concealed, easy-clean aerator
- Includes click drain
- Includes escutcheon
- 235 mm spout reach

Codes/Standards Applicable


Specified model meets or exceeds the following:

- GB 18145-2014

Installation Notes

Install this product according to the installation guide.


WALL-MOUNT LAVATORY SPOUT K-23888T



Specified Model

Model	Description	Color/Finished	
K-23888T	Components wall-mount lavatory spout-ribbon	☐ CP: Polished Chrome	☐ Others
Required Accessories			
K-28138T	Components wall-mount single control handle lavatory faucet valve	☐ CP: Polished Chrome	☐ Others
K-77980T-4	Components wall-mount single control lavatory handle-lever	☐ CP: Polished Chrome	☐ Others


For a full range of color finishes in your market please contact your local Kohler representative.



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

หัวก๊อกผสมอ่างล้างหน้าแบบติดผนัง K-23888T

คุณลักษณะ

- ผลิตจากทองเหลือง
- วัสดุเคลือบผิวพิเศษจากโคห์เลอร์ คงทน เงางาม
- ดีไซน์แบบซ่อนปากก๊อก ง่ายต่อการทำความสะอาด
- พร้อมสวิตช์อ่างแบบกด
- พร้อมฝาครอบ
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 235 มม.


มาตรฐาน

คุณสมบัติตามมาตรฐาน

- GB 18145-2014

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง



รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-23888T	หัวก๊อกผสมอ่างล้างหน้าแบบติดผนัง ปากก๊อก-รีบบิ้น รุ่นคอมโพเนนท์	☐ CP: สีสโครเมจ ☐ อื่นๆ
อุปกรณ์ที่จำเป็น		
K-28138T	ชุดวาล์วหัวก๊อกผสมอ่างล้างหน้าแบบติดผนัง รุ่นคอมโพเนนท์	☐ CP: สีสโครเมจ ☐ อื่นๆ
K-77980T-4	มือบิดหัวก๊อกผสมอ่างล้างหน้าแบบติดผนัง มือบิดแบบก้านโยก รุ่นคอมโพเนนท์	☐ CP: สีสโครเมจ ☐ อื่นๆ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน




กราฟแสดงอัตราการไหล

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์