

### TH3 WAY COLUMN W/MF SHOWERHEAD K-23860T

#### Features

- Durable Kohler finishes resist corrosion and tarnishing
- Adjustable inlet fittings with 10 mm tolerance
- Intuitive control by one touch of a button changes water outlet and water volume
- Precise thermostatic temperature control with over-ridable temperature stop
- Extra-large control panel serves as a stylish and useful storage shelf
- Includes bath outlet
- Includes showerhead
- Includes 3-function handshower

#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552
- GB/T 23447-2009

#### Installation Notes


Install this product according to the installation guide.




#### Specified Model

Model	Description	Color/Finishes	
K-23860T-9	Urbanity+ thermostatic shower column	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others


For a full range of color finishes in your market please contact your local Kohler representative.



**Flow Curve (Bath outlet)**




**Flow Curve (Showerhead)**



**Flow Curve (Handshower)**

Note: Flow rate are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.  
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

## Product Diagram

### คุณลักษณะ

- วัสดุเคลือบผิวพิเศษจากโคห์เลอร์ คงทน เงามาม
- อุปกรณ์ติดตั้งกับท่อน้ำเข้าปรับระยะได้ 10 มม.
- การควบคุมที่ใช้งานง่ายเพียงปุ่มเดียวสำหรับเปลี่ยนช่องจ่ายน้ำและปริมาณน้ำ
- ระบบเทอร์โมสแตติกควบคุมอุณหภูมิแม่นยำ พร้อมตัวหยุดนิรภัย
- แผงควบคุมขนาดใหญ่พิเศษทำหน้าที่เป็นชั้นวางของที่มีสไตล์และมีประโยชน์
- พร้อมปากก๊อกอ่างอาบน้ำ
- พร้อมฝักบัวก้านแข็ง
- พร้อมฝักบัวสายอ่อนปรับสายน้ำได้ 3 ระดับ

### มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552
- GB/T 23447-2009

### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกผสมลงอ่างอาบน้ำและยืนอาบ พร้อมชุดฝักบัวสายอ่อนและชุดฝักบัวก้านแข็ง


## K-23860T




### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-23860T-9	ก๊อกผสมลงอ่างอาบน้ำและยืนอาบระบบเทอร์โมสแตติกพร้อมฝักบัวสายอ่อนและชุดฝักบัวก้านแข็ง รุ่นเออร์เบนิที+	<input type="checkbox"/> CP: สีโครมเงา	<input type="checkbox"/> สีอื่นๆ


ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



กราฟแสดงอัตราการไหล (อ่างอาบน้ำ)




กราฟแสดงอัตราการไหล (ฝักบัวก้านแข็ง)



กราฟแสดงอัตราการไหล (ฝักบัวสายอ่อน)

หมายเหตุ: อัตราการไหลโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ  
 หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์