

Features

- Vitreous china
- Elongated bowl
- Skirted bowl
- Includes wrapped seat or nightlight seat or slim seat
- Includes polished chrome push button
- Wash down flushing system
- Dual flush 2.6/4 liter per flush
- 305 mm rough-in for S-trap
- 680 x 370 x 745 mm

Codes/Standards Applicable


Specified model meets or exceeds the following:

- SS 574

ONE-PIECE TOILET WITH SEAT

K-28628K

ALSO K-28631K/28633K



Technical Information

Fixture:	
Configuration	one-piece, elongated
Water per flush	2.6/4 liter
Passageway	51 mm
Water area	127 x 102 mm
Water depth from rim	230 mm
Seat post hole centers	140 mm

Included Components:	
Tank cover	1337868-SP-**
Wrapped seat (for K-28631K) or Nightlight seat (for K-28633K) or Slim seat (for K-28628K)	K-28770K K-28767K K-28773K
S-Trap connector assy	1084337-A

Specified Model


Model	Description	Color/Finished
K-28628K	Reach Up one-piece toilet, S-Trap with slim seat	0: White
K-28631K	Reach Up one-piece toilet, S-Trap with wrapped seat	0: White
K-28633K	Reach Up one-piece toilet, S-Trap with nightlight seat	0: White

Installation Notes

Install this product according to the installation guide.

Recommended Accessories		Color/Finished
1065832	Water supply hose, stainless	CP: Polished Chrome
1265885-SP	Shut off valve	CP: Polished Chrome
1138552	P-Trap connector	N/A

Dimensions are approximate.
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

Product Diagram