

Features

- Solid metal construction
- Durable KOHLER finishes resist corrosion and tarnishing
- Leak-free ceramic disc valve with lifetime warranty
- Lift and turn handle operation
- Easy, Sealant-free installation

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.18.1.2012
- EN 817-2008
- GB 18145-2014

Installation Notes

Install this product according to the installation guide.

RECESSED BATH AND SHOWER VALVE TRIM-AVID

K-97366T-B4
ALSO K-97365T-B4




Specified Model


Model	Description	Color/Finished
K-97366T-B4	Modulo recessed bath and shower valve trim-Avid	CP: Polish chrome
K-97365T-B4	Modulo recessed shower valve trim-Avid	CP: Polish chrome

For a full range of color finishes in your market please contact your local Kohler representative.

Required Accessories		
K-98699T-B	Modulo universal box	NA




Flow Curve (Bath outlet)



Flow Curve (Shower outlet)

K-97366T-B4






Flow Curve

K-97365T-B4




Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



K-97366T-B4



K-97365T-B4

Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากโลหะ
- วัสดุเคลือบผิวพิเศษของโครห์เลอร์ คงทน เงางาม
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- โยกและหมุนเพื่อใช้งานมือปิด
- ติดตั้งง่าย ป้องกันน้ำรั่วซึม

มาตรฐาน

คุณสมบัติตามมาตรฐาน :

- ASME A112.18.1.2012
- EN 817-2008
- GB 18145-2014

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ชุดฝาคกรอบและวาล์วผสมน้ำ
กำแพงล่างอ่างและยืนอาบ

K-97366T-B4

และ **K-97365T-B4**




รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-97366T-B4	ชุดฝาคกรอบและวาล์วผสมน้ำกำแพงล่างอ่างและยืนอาบ รุ่นโมดูล อะวี่ด	CP: สีโครมเงา
K-97365T-B4	ชุดฝาคกรอบและวาล์วผสมน้ำกำแพงยืนอาบ รุ่นโมดูล อะวี่ด	CP: สีโครมเงา

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโครห์เลอร์ในประเทศของท่าน

อุปกรณ์ที่จำเป็น		
K-98699T-B	กล่องติดตั้งวาล์วโมดูล	NA




กราฟแสดงอัตราการไหล (ก๊อกอ่างอาบน้ำ)



กราฟแสดงอัตราการไหล (ฝักบัวอาบน้ำ)

K-97366T-B4






กราฟแสดงอัตราการไหล




K-97365T-B4

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



K-97366T-B4



K-97365T-B4

หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์