

Features

- Brass and Premium metal construction.
- Durable Kohler finishes resist corrosion and tarnishing.
- Includes installation hardware.
- Coordinates with other product in the Complements collection.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- N/A

Installation Notes

Install this product according to the installation guide.




CAUTION: Risk of personal injury Do not install these products in any area where they are likely to be used inadvertently as a grab bar or support bar. These products are not designed or intended for use as a grab bar or support bar.

Specified Model

Model	Description	Color/Finishes	
K-78372T	Component 18" Towel Bar	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-78373T	Component 24" Towel Bar	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-78375T	Component 24" DoubleTowel Bar	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-78376T	Component 24" DoubleTowel Shelf	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-78377T	Component Towel Arm	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-78378T	Component Robe Hook	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-78379T	Component Double Towel Arm	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-78382T	Component TP Holder	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-78383T	Component Vertical TP Holder	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-78384T	Component Covered Double TP Holder	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)


Unit: mm




K-78372T

Product Diagram


Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



K-78373T




K-78375T







K-78376T

Product Diagram





Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



K-78377T




K-78378T




K-78379T

Product Diagram


Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



K-78382T



K-78383T



K-78384T

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลืองและโลหะ
- วัสดุเคลือบผิวพิเศษของโคห์เลอร์ คงทน เงางาม
- พร้อมอุปกรณ์ติดตั้ง
- เหมาะกับผลิตภัณฑ์ชุดคอมโพนেন্ট

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ไม่ระบุ

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง




ข้อควรระวัง: ความเสี่ยงซึ่งอาจทำให้ได้รับบาดเจ็บ
ผลิตภัณฑ์นี้ไม่ได้ออกแบบมาเพื่อเป็นการจับ หรืออุปกรณ์ค้ำยัน
ห้ามติดตั้งอุปกรณ์นี้ในบริเวณที่สามารถใช้เป็นจุดค้ำยันได้

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
		CP: สีโครมเงา	อื่นๆ
K-78372T	ราวแขวนผ้าเดี่ยว 18" รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>
K-78373T	ราวแขวนผ้าเดี่ยว 24" รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>
K-78375T	ราวแขวนผ้าคู่ 24" รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>
K-78376T	ชั้นตะแกรงพร้อมราวแขวน 24" รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>
K-78377T	ขอแขวนผ้าเช็ดตัว รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>
K-78378T	ขอแขวนผ้า รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>
K-78379T	ขอแขวนผ้าเช็ดตัวคู่ รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>
K-78382T	ที่ใส่กระดาษชำระ รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>
K-78383T	ที่ใส่กระดาษชำระแนวตั้ง รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>
K-78384T	ที่ใส่กระดาษชำระแบบคู่มือพับปิด รุ่นคอมโพนেন্ট	<input type="checkbox"/>	<input type="checkbox"/>

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)


หน่วย: มม.




K-78372T

ภาพแสดงผลิตภัณฑ์


ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
 หน่วย: มม.



K-78373T




K-78375T







K-78376T

ภาพแสดงผลิตภัณฑ์





ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
 หน่วย: มม.



K-78377T




K-78378T




K-78379T

ภาพแสดงผลิตภัณฑ์


ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
 หน่วย: มม.



K-78382T



K-78383T



K-78384T

ภาพแสดงผลิตภัณฑ์