

Features

- Brass construction.
- Durable KOHLER finishes resist corrosion and tarnishing.
- Laminar flow aerator for clean aesthetic and reduced splash (K-EX27029T-9).
- 116 mm spout reach (K-EX27029T-9).
- Adjustable inlet fittings with 15 mm tolerance.
- Precise thermostatic temperature control with over-ridable temperature stop.
- Includes 3-function handshower.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552 • QB 2806-2017

Installation Notes

Install this product according to the installation guide.

EXPOSED WALL-MOUNT
BATH SHOWER MIXER
K-EX27028T-9
ALSO K-EX27029T-9




Specified Model



Model	Description	Colors/Finishes	
K-EX27028T-9	Occasion exposed wall-mount shower mixer	☐ CP: Polished Chrome	☐ Others
K-EX27029T-9	Occasion exposed wall-mount bath shower mixer	☐ CP: Polished Chrome	☐ Others

For a full range of color finishes in your market, please contact your local Kohler representative.

EX27028T-9





EX27029T-9



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- วัสดุเคลือบผิวพิเศษจากโคโธเลอร์คิงทงเงางาม
- สายน้ำของก๊อกน้ำสัมผัสอ่อนนุ่ม ลดการกระจายตัวของสายน้ำ (K-EX27029T-9)
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 116 มม. (K-EX27029T-9)
- อุปกรณ์การติดตั้งกับทางน้ำเข้าปรับระยะได้ 15 มม.
- ระบบเทอร์โมสแตติก ควบคุมอุณหภูมิแม่นยำ พร้อมปุ่มหยุดนิรภัย
- พร้อมฝักบัวสายอ่อนปรับสายน้ำ 3 ระดับ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552 • QB 2806-2017

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกผสมอ่างอาบน้ำและยืนอาบ
แบบติดผนังพร้อมฝักบัวสายอ่อน

K-EX27028T-9
และ **K-EX27029T-9**




รุ่นผลิตภัณฑ์



รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-EX27028T-9	ก๊อกผสมยืนอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นไอเคชั่น	☐ CP: สีโครมเงา	☐ อื่นๆ
K-EX27029T-9	ก๊อกผสมอ่างอาบน้ำและยืนอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นไอเคชั่น	☐ CP: สีโครมเงา	☐ อื่นๆ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคโธเลอร์ในประเทศของท่าน

EX27028T-9




EX27029T-9




หมายเหตุ: อัตราการไหลคือโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



EX27028T-9



EX27029T-9

หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์