

Features

- Brass construction.
- Durable Kohler finishes resist corrosion and tarnishing.
- Adjustable inlet fittings with 15 mm tolerance.
- Optimized sprayface and large nozzles with Katalyst® Air-induction.
- Precise thermostatic temperature control with over-ridable temperature stop.
- Includes 1-function showerhead.
- Includes 3-function handshower.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552 • QB 2806-2017

Installation Notes

Install this product according to the installation guide.


SHOWER COLUMN
K-23125T-B9




Specified Model

Model	Description	Colors/Finishes
K-23125T-B9	July thermostatic 3-way shower column	Matte Black


For a full range of color finishes in your market please contact your local Kohler representative.



Flow Curve - Showerhead




Flow Curve - Handshower



Flow Curve - Bath Outlet

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- วัสดุเคลือบผิวพิเศษจากโคโธเลอร์ คงทน เงางาม
- อุปกรณ์ติดตั้งกับท่อน้ำเข้าปรับระยะได้ 15 มม.
- หัวฝักบัวพร้อมรูฝักบัวขนาดใหญ่แบบเรียงตัว ระบบแคตทาลิส เทคโนโลยีการอัดอากาศเพื่อสายน้ำชุ่มฉ่ำเต็มสัมผัส
- ระบบเทอร์โมสแตติก ควบคุมอุณหภูมิแม่นยำ พร้อมปุ่มหยุดนิรภัย
- พร้อมฝักบัวก้านแข็ง 1 ระดับ
- พร้อมฝักบัวสายอ่อนปรับสายน้ำได้ 3 ระดับ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552
- QB 2806-2017

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง




ก๊อกผสมเย็นอาบแบบติดผนังพร้อมชุดฝักบัวสายอ่อนและชุดฝักบัวก้านแข็ง K-23125T-B9



รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-23125T-B9	ก๊อกผสมเย็นอาบแบบติดผนังพร้อมฝักบัวสายอ่อนและฝักบัวก้านแข็ง รุ่นจุลายน	สีดำด้าน

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคโธเลอร์ในประเทศของท่าน



หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง
ภาพแสดงผลิตภัณฑ์