

Features

- Brass construction.
- Leak-free ceramic disc valve(s) with lifetime warranty.
- Durable KOHLER finishes resist corrosion and tarnishing.
- 198 mm spout reach.(K-EX27110T-4)
- 212 mm spout reach.(K-EX27111T-4)
- Includes 3-function handshower.

DECK-MOUNT BATH AND SHOWER FAUCET WITH HANDSHOWER AND DIVERTER K-EX27110T-4, K-EX27111T-4

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552 • GB 18145-2014

Installation Notes


Install this product according to the installation guide.




Specified Model

Model	Description	Colors/Finishes	
K-EX27110T-4	Occasion deck-mount bath and shower faucet with handshower and diverter	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-EX27111T-4	Occasion deck-mount bath and shower faucet with handshower and diverter	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others

For a full range of color finishes in your market, please contact your local Kohler representative.




Flow Curve (Bath outlet)




Flow Curve (Handshower)

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



K-EX27110T-4



K-EX27111T-4

Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษจากโคโธเลอรัคทนเงางาม
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 198 มม.(K-EX27110T-4)
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 212 มม.(K-EX27111T-4)
- พร้อมฝักบัวสายอ่อนปรับสายน้ำ 3 ระดับ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552 • GB 18145-2014

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง



ก๊อกผสมลงอ่างอาบน้ำ พร้อมฝักบัวสายอ่อนและตัวปรับทางน้ำ K-EX27110T-4, K-EX27111T-4



รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-EX27110T-4	ก๊อกผสมลงอ่างอาบน้ำพร้อมฝักบัวสายอ่อนและตัวปรับทางน้ำ รุ่นไอเคชั่น	<input type="checkbox"/> CP: สีโครมเงา	<input type="checkbox"/> อื่นๆ
K-EX27111T-4	ก๊อกผสมลงอ่างอาบน้ำพร้อมฝักบัวสายอ่อนและตัวปรับทางน้ำ รุ่นไอเคชั่น	<input type="checkbox"/> CP: สีโครมเงา	<input type="checkbox"/> อื่นๆ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคโธเลอรัคในประเทศของท่าน




หมายเหตุ: อัตราการไหลโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.



K-EX27110T-4



K-EX27111T-4

หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง
ภาพแสดงผลิตภัณฑ์