

Features

- Brass construction.
- Durable Kohler finishes resist corrosion and tarnishing.
- Laminar flow aerator for clean aesthetic and reduced splash.
- Adjustable inlet fittings with 15 mm tolerance.
- 116 mm spout reach.
- Adjustable inlet fittings with 15 mm tolerance.
- Precise thermostatic temperature control with over-ridable temperature stop.
- Includes 1 function showerhead.
- Includes 3 functions handshower.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552 • GB 18145-2014
- QB/T 2806-2017


Installation Notes

Install this product according to the installation guide.


Specified Model

Model	Description	Colors/Finishes	
K-EX27033T-9	Occasion 3-way thermostatic shower column	☐ CP: Polished Chrome	☐ Others


For a full range of color finishes in your market please contact your local Kohler representative.



Flow Curve (Showerhead)




Flow Curve (Handshower)



Flow Curve (Bath outlet)

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- วัสดุเคลือบผิวพิเศษจากโคห์เลอร์ คงทน เงางาม
- สายน้ำสัมผัสอ่อนนุ่ม ลดการกระจายตัวของสายน้ำ
- ระยะจากกึ่งกลางตัวก๊อกถึงกลางปากก๊อก 116 มม.
- อุปกรณ์ติดตั้งกับทางน้ำเข้าปรับระยะได้ 15 มม.
- ระบบควบคุมอุณหภูมิเทอร์โมสแตติก พร้อมเทคโนโลยีป้องกันน้ำลวก
- พร้อมฝักบัวก้านแข็งปรับสายน้ำ 1 ระดับ
- พร้อมฝักบัวสายอ่อนปรับสายน้ำได้ 3 ระดับ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552 • GB 18145-2014
- QB/T 2806-2017

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกผสมลงอ่างอาบน้ำและยืนอาบพร้อม
ชุดฝักบัวสายอ่อนและชุดฝักบัวก้านแข็ง


K-EX27033T-9




รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-EX27033T-9	ก๊อกผสมลงอ่างอาบน้ำและยืนอาบระบบเทอร์โมสแตติกพร้อมชุดฝักบัวสายอ่อนและฝักบัวก้านแข็ง รุ่นโอเคชั่น	☐ CP: สีโครมเงา	☐ อื่นๆ


ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



กราฟแสดงอัตราการไหล (ฝักบัวก้านแข็ง)




กราฟแสดงอัตราการไหล (ฝักบัวสายอ่อน)



กราฟแสดงอัตราการไหล (ก๊อกลงอ่างอาบน้ำ)

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์