

Features


- Vitreous china
- Elongated bowl
- Non back to wall
- Includes wrapped seat or double injection slim seat or slim seat
- Includes polished chrome trip lever
- Wash Down Flushing system
- Dual flush 3/4.5 liter per flush
- 305 mm rough-in for S-trap
- 680 x 380 x 752 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 792
- ASME A112.19.2/CSA B45.1
- MS 1522
- SS 574

TWO-PIECE TOILET WITH SEAT K-31190K ALSO K-31191K/31192K



Technical Information

Fixture:	
Configuration	two-piece, elongated
Water per flush	3/4.5 liter
Passageway	51 mm
Water area	127 x 102 mm
Water depth from rim	225 mm
Seat post hole centers	140 mm

Included Components:	
Bowl	K-31189K
Tank	K-23625K
Tank cover	1369030
Slim seat (for K-31190K) or Double injection seat (for K-31191K) or Wrapped seat (for K-31192K)	K-77471K K-77070K K-5574K
S-Trap connector	1084337-A

Specified Model


Model	Description	Color/Finished
K-31190K	Veil two-piece toilet, S-trap with slim seat	0: White
K-31191K	Veil two-piece toilet, S-trap with double injection slim seat	0: White
K-31192K	Veil two-piece toilet, S-trap with wrapped seat	0: White

Required Accessories		Color/Finished
1065832	Water supply hose, stainless	CP: Polished Chrome
1265885-SP	Shut off valve	CP: Polished Chrome

Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.
Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

Product Diagram