

### Features

- Vitreous china
- Elongated bowl
- Skirted bowl
- Includes polished chrome push button
- Wash down flushing system
- Dual flush 3/4.5 liter per flush
- 305 mm rough-in for S-trap
- 680 x 370 x 745 mm

### Codes/Standards Applicable

Specified model meets or exceeds the following:

- MS 1552
- TIS 792
- SS 574
- ASME 112.19.2/CSA B45

## ONE-PIECE TOILET WITH SEAT K-28630K-HC



### Technical Information

Fixture:	
Configuration	one-piece, elongated
Water per flush	3/4.5 liter
Passageway	51 mm
Water area	127 x 102 mm
Water depth from rim	230 mm
Seat post hole centers	140 mm

Included Components:	
Tank cover	1337868-SP-**
S-Trap connector assy	1084337-A

### Specified Model

Model	Description	Color/Finished
K-28630K-HC	Reach Up one-piece toilet, S-Trap	0: White


Recommended Accessories		Color/Finished
1065832	Water supply hose, stainless	CP: Polished Chrome
1265885-SP	Shut off valve	CP: Polished Chrome
1138552	P-Trap connector	N/A

### Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

### Product Diagram