

TWO-PIECE TOILET K-31116K-HC

Features

- Vitreous china
- Elongated bowl
- Skirted bowl
- Includes polished chrome push button
- Wash down flushing system with rimless technology
- Dual flush 2.6/4 liter per flush
- 305 mm rough-in for S-trap
- 660 x 395 x 750 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- SS 574



Technical Information

| | |
|------------------------|------------------------|
| Fixture: | |
| Configuration | two-piece, round-front |
| Water per flush | 2.6/4 liter |
| Passageway | 51 mm |
| Water area | 127 x 102 mm |
| Water depth from rim | 235 mm |
| Seat post hole centers | 140 mm |

| | |
|-----------------------|---------------|
| Included Components: | |
| Bowl | 31113K-HC |
| Tank | 21010R |
| Tank cover | 1335596-SP-** |
| S-Trap Connector Assy | 1084337-A |

Installation Notes

Install this product according to the installation guide.


Specified Model

| Model | Description | Color/Finished |
|-------------|-----------------------------------|----------------|
| K-31116K-HC | Reach Up two-piece toilet, S-Trap | 0: White |

| Recommended Accessories | | |
|-------------------------|------------------------------|---------------------|
| 1065832 | Water Supply Hose, Stainless | CP: Polished Chrome |
| 1265885-SP | Shut Off Valve | CP: Polished Chrome |
| 1138552 | P-Trap connector | N/A |

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

Product Diagram