

### TWO-PIECE TOILET K-31117K-HC

#### Features

- Vitreous china
- Elongated bowl
- Skirted bowl
- Includes polished chrome push button
- Wash down flushing system with rimless technology
- Dual flush 3/4.5 liter per flush
- 305 mm rough-in for S-trap
- 660 x 395 x 750 mm

#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- BS:EN 997
- TIS 792
- MS 1522
- ASME 112.192 / CSA B45
- SS 574



#### Technical Information

Fixture:	
Configuration	two-piece, round-front
Water per flush	3/4.5 liter
Passageway	51 mm
Water area	127 x 102 mm
Water depth from rim	235 mm
Seat post hole centers	140 mm

Included Components:	
Bowl	31113K-HC
Tank	21003K
Tank cover	1335596-SP-**
S-Trap Connector Assy	1084337-A

#### Installation Notes


Install this product according to the installation guide.

#### Specified Model

Model	Description	Color/Finished
K-31117K-HC	Reach Up two-piece toilet, S-Trap	0: White

Recommended Accessories		
1065832	Water Supply Hose, Stainless	CP: Polished Chrome
1265885-SP	Shut Off Valve	CP: Polished Chrome
1138552	P-Trap connector	N/A

Dimensions are approximate.  
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.  
Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

#### Product Diagram