


Features

- Vitreous china
- Skirted bowl
- Includes slim seat
- Includes polished chrome push button
- Wash down flushing system
- Dual flush 3/4.5 liter per flush
- 305 mm rough-in for S-trap
- 680 x 370 x 745 mm

ONE-PIECE TOILET WITH SEAT K-28627K-ITSL



Codes/Standards Applicable

Specified model meets or exceeds the following:

- MS 1552
- TIS 792
- SS 574
- ASME 112.19.2/CSA B45

Technical Information

Fixture:	
Configuration	one-piece
Water per flush	3/4.5 liter
Passageway	51 mm
Water area	127 x 102 mm
Water depth from rim	230 mm
Seat post hole centers	140 mm

Included Components:	
Tank cover	1337868-SP-**
Slim seat	K-28773K
S-Trap connector assy	1084337-A
Continuous Clean Dosing Unit	1435128

Specified Model

Model	Description	Color/Finished
K-28627K-ITSL	Reach Up one-piece toilet, S-Trap with slim seat	0: White


Recommended Accessories		Color/Finished
1065832	Water supply hose, stainless	
1265885-SP	Shut off valve	CP: Polished Chrome
1138552	P-Trap connector	

Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

Product Diagram