

Features

- Ceramic remote valve for single-lever control.
- Smooth design lines facilitate cleaning.
- Fluid design lines for ease of cleaning.
- 15.0 gpm (56.8 l/min) @ 45 psi

Material

- KOHLER finishes resist corrosion and tarnishing.
- Solid brass construction for durability and reliability.
- Premium Metal Construction.

Installation

- Mounting on deck.



Codes/Standards

None Applicable


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	CP	Polished Chrome
--	----	-----------------



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 9.92 gal/min (37.6 l/min)

Pressure: 60 psi (4.1 bar)

Spout:

Spout reach: 5-7/8" (149 mm)

Notes

Install this product according to the installation instructions.