

BEFORE YOU BEGIN

- Please read these instructions carefully to familiarize yourself with the required tools, materials, and installation sequences. Follow the sections that pertain to your particular installation. This will help you avoid costly mistakes. In addition to proper installation, read all operating and safety instructions.
- All information in these instructions is based upon the latest product information available at the time of publication. Kohler China. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.
- These instructions contain important care, cleaning, and warranty information-**please leave instructions for the consumer.**
- MaxiSpace cabinet adopts E0 grade wood-based panel of high quality, and with further processing, its formaldehyde emissions will be less than 0.05mg/m³.
- Turn off the water supply.
- The plumbing installation must comply with Water Supply Regulations/Bye-laws, Building Regulations or any particular regulations and practices, specified by the local water company or water undertakers. The installation should be carried out by a plumber.
- Before installation carefully inspect the new fixture for any signs of damage.
- This product complies with GB/T 24977-2024, LY/T 1279-2020.
- The temperature of use or transportation of this product shall not be higher than 60°C.

安装之前

- 请仔细阅读本指引，以便熟悉所需工具、物料及安装程序。请遵照适用的章节来安装本产品，以免安装失当导致不必要的损失。除了有关正确的安装方法之外，还务请详阅所有操作及安全指引。
- 本指引所载之一切资料，均以印刷时所有之最新产品情况为基础，科勒中国保留权利随时更改产品特性、包装或供应情况，恕不另行通知。安装家具之前，请先确认所有必需的电气工作均已完成。
- 本指引也包含了有关保养、清洁及担保等重要资料-请交予用户保存。
- 博纳浴室柜选用E0级优质饰面人造板精心加工而成，其甲醛释放量少于0.05mg/m³。
- 关闭供水。
- 管道安装必须遵循当地所有给排水、建筑或者其他的特别规定。管道安装人员必须具备相应资格。
- 安装之前，仔细检查新产品是否有损伤。
- 本产品符合GB/T 24977-2024、LY/T 1279-2020。
- 本产品使用或运输温度不得高于60°C。

ORDERING INFORMATION

This installation covers the following products in the MaxiSpace range:

Maxispace Cabinet 600mm.....	K-27443T
Maxispace Cabinet 900mm.....	K-27444T

订购信息

此安装说明书适用于以下博纳系列家具的安装：

博纳浴室柜600mm	K-27443T
博纳浴室柜900mm	K-27444T

SAFETY WARNINGS

Kohler products are precision-engineered and should give continued superior and safe performance, provided:

1. They are installed, commissioned, operated and maintained in accordance with the recommendations given in this Manual.
2. Periodic attention is given, as necessary, to maintain the product in good functional order. Recommended guidelines are given in the **MAINTENANCE** section.

Carefully inspect the new fixture for any signs of damage.

When installing Kohler Products, manufacturers guidelines for power tool safety should be followed.

安全警告

科勒产品经过精确制造，性能卓越，经久耐用。为保证产品品质，您必须：

1. 按照此手册中推荐的方法进行安装、起动、操作及维护。
2. 如有需要，定期检查，令产品保持良好性能状态。日常维护章节中列有推荐方法。

仔细检查新产品是否有损伤。

在安装科勒产品时，必须遵循制造商相关电动工具的安全的指令。


KOHLER CHINA INVESTMENT CO., LTD NO.158, JIANG CHANG SAN ROAD,
 JING'AN DISTRICT, SHANGHAI, PRC POST CODE: 200436
 科勒(中国)投资有限公司 上海市静安区江场三路158号 邮编：200436

ROUGHING-IN


尺寸图

Reference
参考值

UNIT : mm
单位: 毫米



K-27443T
Maxispace Cabinet 600mm
博纳浴室柜600mm



K-27444T
Maxispace Cabinet 900mm
博纳浴室柜900mm

Fig.1
图1

Kohler reserves the right to change marked dimensions without prior notice.
科勒公司保留随时变更图中标示尺寸的权利，无需另行通知。

INSTALLATION

安装

A. Install Washbasin Cabinet

Install the services.
Hot (H) and Cold (C) inlets must be connected to the correct inlet pipes.
Install the drain in accordance with the manufacturer's instructions.
We suggest using P-trap drain. Connect P-trap pipe with washbasin drain.

Caution! Make sure a watertight seal exists on all washbasin drain connections.

Caution! Provide access to the plumbing connections for future plumbing maintenance.

The hot and cold water supplies must be installed with isolating valves.

A. 安装脸盆柜

安装管道
热水(H)及冷水(C)入口必须连接至正确的进水管。

根据制造商说明书安装排水。

我们建议采用墙排水方式，使用P弯管连接脸盆去水。

小心! 请确保所有脸盆排水的连接处都装有防水密封圈。

小心! 管道连接处需留有检修空间，以备日后管道维护之用。

注意! 安装冷热供水管时必须使用隔离阀。




Fig.2
图2

1. Mark the position of hanged bracket and wall bolt according to dimensions as illustrated, and loosen the suspension hook of washbasin cabinet.



Caution! Avoid the cables and pipes inner set when drilling in the wall.

Note: Different types of bolts are required for different decoration boards. Please apply suitable bolts and plugs.

1. 根据图示尺寸在墙壁上标示出挂墙托片和配套台盆悬挂螺栓的位置，并将脸盆柜吊码的挂钩伸长。



小心! 在墙壁上钻孔时请务必小心避开内设的缆线和管道。

注意: 不同的装饰墙面需要不同型号的螺钉。请使用合适的螺钉和入墙胶塞。




Fig.3
图3

2. Drill holes for fixing the bracket and bolt. Using a level to ensure that the hanged bracket is level.

3. Use suitable plugs and bolts, and fix the bracket and bolt on the wall. Fix the bolts supplied with the vanity on the wall. Each bolt shall be 65-75mm out of the wall.

4. Fix metal leg: Place the cabinet upside down as shown in Fig.4. Take out the metal leg and screw supplied from the package. Fix the metal leg to the hole in middle of the cabinet bottom. (The cabinet is supplied with only one metal leg that is to be fixed to prevent the cabinet from descending. Please purchase Kohler metal leg K-76082T-LK for additional needs.)

2. 钻好挂墙托片柜体固定孔及台盆悬挂螺栓的安装孔。使用水平仪检查，确保挂墙托片水平。

3. 使用合适的入墙胶塞和螺钉，将挂墙托片和柜体固定膨胀管固定在墙上。配套台盆配件中的悬挂螺栓也固定在墙上，并依照台盆说明书要求使每个螺栓保持外露约65-75mm。

4. 安装中脚: 将浴室柜放倒如下图4，打开包装内标配的铝脚和螺丝，按浴柜底板中部的引孔固定中脚。(浴柜标配一个中脚,目的是防止底板下垂,如有需要安装另外的脚,请购买科勒产品铝脚K-76082T-LK)




Fig.4
图4

5. Apply silicone sealant onto the contact surface of the cabinet and vanity. Wait for the sealant to cure. (Install adjustable feet first if needed.)

6. Fix faucet and drain according to their installation instructions.

7. Fix onto wall.

- Lift the cabinet and vanity by two people. Align the vanity hanging hole with the bolts on the wall. Make the bolts through the vanity hanging hole.
- Hang the two back wall clips onto the pre-fixed bracket on the wall.




Fig.5
图5

5. 将柜体与台盆接触的部位用硅胶枪均匀地涂上硅胶，待胶干。（如需安装地脚，请按地脚说明书先装地脚再装盆。）

6. 按照龙头和落水的制造商的安装说明安装龙头和落水。

7. 与墙面固定

- 由两人稍稍抬起柜体和台盆，先将台盆悬挂孔对准墙面预先打好的台盆悬挂螺栓，使螺栓穿过台盆孔。
- 将柜体后部的2个挂钩挂在墙面预先安装好的托墙挂片上。




Fig.6
图6

c. Adjust the cabinet and vanity level. Put the cabinet against the wall by adjusting the screws of wall clips.

c. 将脸盆柜和台盆调节到水平状态，调节吊码的螺钉，使脸盆柜背板紧贴墙壁。




Fig.7
图7

d. Fix the cabinet and vanity again with the bolts according to pre-drilled cabinet fixing holes on the wall.

d. 按照墙上预先打好的柜体固定孔将柜体与墙面再次使用膨胀螺杆固定。

e. Open the cabinet door and the drawer. Fix the bolt according the vanity installation instructions. Before that, please apply silicone sealant onto the contact surface of the vanity and the wall.

e. 将柜体的门和抽屉打开，按照台盆说明书固定悬挂螺栓。固定前用硅胶枪在台盆与墙面接触面均匀涂上硅胶。




Fig.8
图8




Fig.9
图9

8. Connect water pipe and drain by professionals to ensure there is no leakage.

Note: Different types of bolts are required for different decoration boards. Please apply suitable bolts and plugs.

Connect Drainage

a. Inwall drainage (P-Trap)

Please install the drain assembly and faucet as shown. Please set the water supply and drainage position according to the suppliers instructions. You can put the pipe into the U Notch.

b. Floor drainage (S-Trap)

Please install the drain assembly and faucet as shown. Please set the water supply and drainage position according to the suppliers instructions. You can put the pipe into the U Notch.




Fig.10
图10

8. 由专业人员连接安装上下水，确保无渗漏。

注意：不同的装饰墙面需要不同型号的螺钉。请使用合适的螺钉和入墙胶塞。

连接排水管

a. 入墙式排水管(P弯管)

请按照如图所示安装排水管和龙头。请遵照供应商所提供的说明在墙上设置进/排水管位置。您可以把弯管放入U形缺口。

b. 地排水 (S弯管)

请按照如图所示设置排水管和龙头。请遵照供应商所提供的说明设进水管位置。您可以把弯管放入U形缺口。




Fig.11
图11

9. Adjust the cabinet.

a. Place the hinge cover and plastic cover(in the hardware pack).

b. Adjust the hinge of door in 3 direction to make sure the door level.




Fig.12
图12

9. 调节浴室柜。

a. 装上门铰盖，盖上塑料孔盖（五金包内）。

b. 如图所示三向调节门板位置。

c. Adjust the screw at middle of the metal leg to make it long enough to firmly contact the ground.

Note: The metal leg is an important part that must be installed to prevent the cabinet from descending. Make sure it firmly contacts the ground.

c. 调节中脚底部螺杆,使其加长, 确保中脚与地面紧密接触.

注意: 中脚是防止柜体下垂的重要配件, 必须安装, 且必须与地面紧密接触.




Fig.13
图13

USER MAINTENANCE

日常维护

Warning! Risk of product damage.

1. Many cleansers contain abrasive and chemical substance which is not suitable for cleaning stainless steel, enamel, plating or plastic products. You may use mild cleansers or soaps to clean the surfaces. Wipe any splashes of cleaner solutions from the surface with clean soft cloth.
2. Maintain ventilation in the bathroom, and separate the dry area from the damp one if conditions permit. Try to open the door and windows of the bathroom and maintain good ventilation.
3. Kohler bathroom cabinet are dealt with strict procedures for damp-proof, whose good damp-proof function ensures good performance even in bathroom of huge humidity. Yet do not splash and pour water directly on the bathroom cabinet. Make sure that the bathroom is not over damp and wipe any splashes from surfaces immediately.
4. Maintenance of door board: Clean and wipe door board regularly, and wipe the condensation vapor with dry and soft cloth.
5. Ensure that electrical connections for appliances such as head lamp is insulated wipe mirror surface with chamois regularly to guarantee the persistent excellent performance.
6. Please do not sit, lean or step on the basin cabinet.
7. If any fixtures caused by abnormal reasons, Kohler China can supply paid replacement for service parts caused by abnormal reasons as shown in the Service Parts Page in the limited duration of warranty.

警告! 小心产品受损。

1. 许多清洁剂都含有研磨剂及化学物质, 不可用于清洁不锈钢、搪瓷、镀层或塑料制品。这些表面须使用温和的清洁剂或皂液进行清洁, 将残余洗涤剂洗干净, 然后用干净的软布擦干。
2. 卫生间请保持良好的通风状态, 有条件的可以干、湿分离, 平常尽量保持浴室空气畅通, 养成开窗开门的习惯。
3. 科勒浴柜都经过严格的防潮处理, 但防潮并不是防水, 使用时不可随意任浴柜被水浇、溅。良好的防潮性能可以保证在高相对湿度时仍有良好使用性, 所以请避免卫生间过于潮湿, 遇有水迹要及时擦干。
4. 门板的保养: 经常用软布定期清洁、擦拭, 洗浴后的冷凝水蒸气应用干布擦净, 保持门板的干爽。
5. 照明灯等电器连接要确保绝缘、防潮镜面最好用麂皮经常擦拭, 可以保障使用质量经久如一。
6. 日常使用时, 请勿坐、倚、靠、踩踏在脸盆柜上。
7. 科勒公司确保在担保期内, 可以提供因非正常原因造成的如维修零件图中零件的有偿更换。