

Features

- Brass construction.
- Leak-free ceramic disc valve with lifetime warranty.
- Durable KOHLER finishes resist corrosion and tarnishing.
- Concealed, easy-clean aerator and key.
- Lever handle(s).
- 189 mm spout reach
- Includes click drain.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB 18145-2014
- TIS 2067-2552

Installation Notes

Install this product according to the installation guide.


SINGLE-HOLE LAVATORY FAUCET K-EX28097T-4/K-EX28098T-4




Specified Model

Model	Description	Color/Finishes	
K-EX28097T-4	Components tall single-hole lavatory faucet	☐ CP: Polished Chrome	☐ Others
K-EX28098T-4	Components super tall single-hole lavatory faucet	☐ CP: Polished Chrome	☐ Others

For a full range of color finishes in your market, please contact your local Kohler representative.



Flow Curve (EX28097T-4)





Flow Curve (EX28098T-4)

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below)

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษของโคห์เลอร์ คงทน เงางาม
- ดีไซน์แบบซ่อนปากก๊อก ง่ายต่อการทำความสะอาด
- มือบิดแบบก้านโยก
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 189 มม.
- พร้อมสวิตช์อ่างแบบกด

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- GB 18145-2014
- มอก. 2067-2552

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


ก๊อกผสมอ่างล้างหน้า รูเดี่ยวแบบก้านโยก K-EX28097T-4/K-EX28098T-4




รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-EX28097T-4	ก๊อกผสมทรงสูงแบบก้านโยก รุ่นคอมโพเนนท์	☐ CP: สีโครมเงา	☐ อื่นๆ
K-EX28098T-4	ก๊อกผสมทรงสูงพิเศษแบบก้านโยก รุ่นคอมโพเนนท์	☐ CP: สีโครมเงา	☐ อื่นๆ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



กราฟแสดงอัตราการไหล (EX28097T-4)




กราฟแสดงอัตราการไหล (EX28098T-4)

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)


ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)

หน่วย: มม.

EX28097T-4



EX28098T-4



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์