

Features

- Vitreous china.
- Round-front bowl.
- Concealed bowl.
- Includes wrapped seat.
- Includes polished chrome push button.
- Wash Down flushing system.
- Dual flush 3/4.5 liter per flush.
- 185 mm rough-in for Plastic P-trap(K-28413H-**).
- 65 mm rough-in for Plastic S-trap(K-28414H-**).
- 680 x 391 x 776 mm


Codes/Standards Applicable

Specified model meets or exceeds the following:

- BS:EN 997

TWO-PIECE TOILET WITH SEAT

K-28413H ALSO K-28414H



Technical Information

Fixture:	
Configuration	two-piece, round-front
Water per flush	3/4.5 liter
Passageway	51 mm
Water area	127 x 102 mm
Water depth from rim	240 mm
Seat post hole centers	140 mm

Included Components:	
Bowl(For K-28413H-**)	28412H-**
Bowl(For K-28414H-**)	29759H-**
Tank	22243H-**
Tank cover	1203722-SP-**
Wrapped seat	K-5574K-**
Plastic P-Trap(For K-28413H-**)	1138552
Plastic S-Trap(For K-28414H-**)	1353009

Specified Model

Model	Description	Color/Finished
K-28413H	Reach Concealed two-piece toilet 3/4.5L, P-trap 185 MM, with Wrapped seat	0: White
K-28414H	Reach Concealed two-piece toilet 3/4.5L, S-trap 65 MM, with Wrapped seat	0: White


Installation Notes

Install this product according to the installation guide.

Recommended Accessories		
1065832	Water Supply Hose, Stainless	CP: Polished Chrome
1265885-SP	Shut Off Valve	CP: Polished Chrome

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

Product Diagram