

Features

- Vitreous china.
- Elongate bowl.
- Wall-faced.
- Includes wrapped seat or nightlight seat or slim set.
- Wash down flushing system.
- 565 x 370 x 446 mm (For seat K-28770K-** and K-28767K-**)
- 565 x 370 x 433 mm (For seat K-28773K-**)

Codes/Standards Applicable


Specified model meets or exceeds the following:

- AS 1172
- BS:EN 997
- GB 6952
- PNS 156
- MS 1552
- SNI 03-0797
- SS 574
- TIS 792
- ASME 112.19.2/CSA B45

Technical Information

Fixture:	
Configuration	Wall-faced, Elongated
Water per flush	2.6/4, 3/4.5 or 3/6 liter
Passageway	51 mm
Water area	125 x 100 mm
Water depth from rim	220 mm
Seat post hole centers	140 mm
*Designed to flush with 2.6/4 lpf, 3/4.5 lpf, 3/6 lpf water when install with a 2/6.4 lpf, 3/4.5 lpf, 3/6 lpf valve.	

WALL-FACED TOILET WITH SEAT K-28765K, K-28768K ALSO K-28771K



Include Components for K-28765K-**	
Bowl	K-28766K-**
Slim seat for K-28765K-**	K-28773K-**
Include Components for K-28768K-**	
Bowl	K-28766K-**
Wrapped seat for K-28768K-**	K-28770K-**
Include Components for K-28771K-**	
Bowl	K-28766K-**
Nightlight seat for K-28771K-**	K-28767K-**

Specified Model


Installation Notes

Install this product according to the installation guide.

Model	Description	Colors/Finishes
K-28765K	Reach up wall-faced toilet, P-Trap with slim seat	0: White
K-28768K	Reach up wall-faced toilet, P-Trap with wrapped seat	0: White
K-28771K	Reach up wall-faced toilet, P-Trap with nightlight seat	0: White
Optional Accessories		
In wall tank frameless (no frame):		
K-32790H-PNE	HT110 IWT W/O F 3.0/4.5 L (H)	
K-32790A-PNE	HT110 IWT W/O F 3.0/4.5 L (A)	
K-32790K-PNE	HT110 IWT W/O F 3.0/4.5 L (K)	
K-32785TW-PNE	HT110 IWT W/O F 3.0/6.0 L (TW)	
K-32792R-PNE	HT110 IWT W/O F 2.6/4.0 L (R)	
K-25443H-PNE	HT201 PNE IWT W/O F 3.0/4.5 L (H)	
K-25443A-PNE	HT201 PNE IWT W/O F 3.0/4.5 L (A)	
K-25443K-PNE	HT201 PNE IWT W/O F 3.0/4.5 L (K)	
K-25444TW-PNE	HT201 PNE IWT W/O F 3.0/6.0 L (TW)	
K-25442R-PNE	HT201 PNE IWT W/O F 2.6/4.0 L (R)	
K-10611A	In-wall tank with cover plate 3.0/4.5 L	
K-10611T	In-wall tank with cover plate 3.0/4.5 L	
K-78073T-PNE	Hydro-Tower 200 PNE IWT 2.6/4.0 L	
K-78073K-PNE	Hydro-Tower 200 PNE IWT 2.6/4.0 L	
K-78076T-PNE	Hydro-Tower 300 PNE IWT 2.6/4.0 L	
K-78076K-PNE	Hydro-Tower 300 PNE IWT 2.6/4.0 L	
K-78074T-PNE	Hydro-Tower 200 PNE IWT 3.0/4.5 L	
K-78074K-PNE	Hydro-Tower 200 PNE IWT 3.0/4.5 L	
K-78077T-PNE	Hydro-Tower 300 PNE IWT 3.0/4.5 L	
K-78077K-PNE	Hydro-Tower 300 PNE IWT 3.0/4.5 L	
K-78075T-PNE	Hydro-Tower 200 PNE IWT 3.0/6.0 L	
K-78075K-PNE	Hydro-Tower 200 PNE IWT 3.0/6.0 L	
K-78078T-PNE	Hydro-Tower 300 PNE IWT 3.0/6.0 L	
K-78078K-PNE	Hydro-Tower 300 PNE IWT 3.0/6.0 L	
Connector:		
1138552	P-Trap connector	
1066987	S-Trap connector	

RACH UP WALL-FACED

Dimensions are approximate. (Do not direct measure a dimensional from picture below)
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.
Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

Product Diagram