Mira Evoco Dual

Mixer Shower

SUITABLE FOR ALL SYSTEMS

5 YEAR WARRANTY

Beauty, built-in. Contemporary, fully-concealed mixer shower - designed for style, reliability and easy installation.





Product Information

Description	Colour	Product No.
Mira Evoco Dual Outlet Shower	Chrome	1.1967.001

Features & Benefits

Temperature control
Thermostatic temperature stability
Easy to fit
Integrated push fit connections already included
Spanner free installation
Mira's innovative installation system, providing a simple first fix solution
Protective cover to minimise damage between first and 2nd fix
Flushing system provided to test connections prior to tiling
Suitable for rear wall and noggin installations
For your customer
Works on all systems, even at low pressure
Separate flow and temperature controls using button actuation
Maximum temperature stop for increased safety (with override for a hotter shower)
Choose your outlet - intuitive push button technology allows you to select the handset, overhead or both
Mira Cool Shield™ to ensure valve doesn't get hot during showering
Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure
One spray 11cm showerhead with rub-clean nozzles
Large 20cm deluge showerhead with rub-clean nozzles
1.25m flexible shower hose

mira SHOWERS


Product Specification

Tech Details

Temperature and flow control
Temperature control type: Thermostatic
Flow actuation: Push button
Installation
Water entry points: Bottom only
Inlet connections: Direct 15mm push fit connections
Outlet connections: 15mm copper pipework
Reversed inlets supported: No = hot left, cold right only
Supply Conditions (hot and cold)
Cold water range: 1°C to 25°C
Hot water range: Min 55°C; 60°C - 65°C (recommended)
Minimum maintained pressure (gas water heater) : 1 bar (10 metre head)
Minimum maintained pressure (gravity system) : 0.1 bar (1 metre head)
Maximum maintained pressure: 5.0 bar (50 metre head)
Maximum static pressure: 10.0 bar (100 metre head)

Performance
Flow rate at 0.5 bar: 8.24 l/min (at Handset), 9.78 l/min (at Deluge)
Flow regulator: 9 l/min (supplied with product - x2)
Temperature stability: ± 2°C
Safety Features
Automatic shutdown: Shutdown within 2 secs
Factory set to safe maximum temperature
Adjustable maximum temperature for on-site conditions
Approvals
KIWA UK approved product
WRAS approved (Water Regulations Advisory Scheme)
TMV2 approved product
CE approved product
UKCA approved product

Dimensions



www.mirashowers.co.uk/expert