

Features

- Solid metal construction.
- Leak-free ceramic disk valve with lifetime warranty.
- Durable KOHLER finishes resist corrosion and tarnishing.
- Flexible G1/2" supply hoses for easy installation.
- 192 mm spout reach.
- Lever handle.
- 360° Swivel spout.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB 18145-2014
- TIS 2067-2552


Installation Notes

Install this product according to the installation guide.

Specified Model

Model	Description	Color/Finishes
K-30946T-4	Kumin Cold Water Flat Spout Swing Kitchen Faucet	CP: Polished Chrome


COLD WATER FLAT SPOUT SWING KITCHEN FAUCET K-30946T-4



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)

Unit: mm



Product Diagram

คุณลักษณะ

- ผลิตจากโลหะ
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษจากโคห์เลอร์ คงทน เงางาม
- สายน้ำดัดขนาด G1/2"
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 192 มม.
- มือบิดแบบก้านโยก
- คอก๊อกหมุนได้ 360 องศา

มาตรฐาน

คุณสมบัติตามมาตรฐาน


- GB 18145-2014
- มอก. 2067-2552

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-30946T-4	ก๊อกเดี่ยวอ่างล้างจาน รุ่นคูมิน	CP: สีโครมเงา



หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 psi)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์