

Features

- Brass construction.
- Leak-free ceramic disc valve with lifetime warranty.
- Durable Kohler finishes resist corrosion and tarnishing.
- Adjustable inlet fittings with 15 mm tolerance.
- Optimized sprayface and large nozzles with Katalyst® Air-induction for improved water coverage.
- Includes 1-function showerhead.
- Includes 3-function handshower.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552 • GB 18145-2014

Installation Notes

Install this product according to the installation guide.


2-WAY SHOWER COLUMN K-97826T-B4




Specified Model

Model	Description	Colors/Finishes
K-97826T-B4	Aleo 2-way shower column	□ CP: Polished Chrome

For a full range of color finishes in your market please contact your local Kohler representative.



Flow Curve (Showerhead)




Flow Curve (Handshower)

Note: Flow rate are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลผลิตจากทองเหลือง
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษจากโคบอลต์ คาร์บอน เงานาม
- อุปกรณ์ติดตั้งกับท่อน้ำเข้าปรับระยะได้ 15 มม.
- หัวฝักบัวพร้อมฝักบัวขนาดใหญ่แบบเรียงตัว ระบบแคตทาลิส เทคโนโลยีการอัดอากาศเพื่อให้น้ำฟุ้งกระจายเต็มสัมผัส
- พร้อมฝักบัวก้านแข็ง 1 ระดับ
- พร้อมฝักบัวสายอ่อนปรับสายน้ำได้ 3 ระดับ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552 • GB 18145-2014


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-97826T-B4	ก๊อคมผสมยีนอาบพร้อมชุดผักบัวสายอ่อนและชุดผักบัวก้านแข็ง รุ่นอาเลโอ	CP: สีโครมเงา

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศไทยของท่าน



กราฟแสดงอัตราการไหล (ฝักบัวก้านแข็ง)




กราฟแสดงอัตราการไหล (ผักบัวสายอ่อน)

หมายเหตุ : อัตราการไหลโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)

หน่วย: มม.



หมายเหตุ: ระยะเวลาแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์