Mira Sport Multi-Fit™

COLD MAINS



Electric Shower

Enjoy long-lasting, powerful performance – from one of the UK's bestselling electric showers.

Product Information

Description	Colour	Product No.
Mira Sport Multi-Fit™ 9.0 kW	White/Chrome	1.1746.833
Mira Sport Multi-Fit™ 9.8 kW	White/Chrome	1.1746.834

Features & Benefits

Temperature contro

Advanced pressure stabilised temperature control

Easy to fit

Retrofits onto inlets of most Mira, Triton, Bristan and Aquilisa electric showers

Adjustable slide bars fit over holes left by previous shower kit

Easy to service

Easy filter access

For vour customer

Separate power and temperature controls

Push button on/of

 $\hbox{Mira Sensi-flo}^{\scriptscriptstyle{\mathsf{TM}}} \ \text{technology helps prevent scalding}$

Mira Clearscale[™] and Dual Element[™] technology reduces limescale by up to 50%

Phased shutdown flushes hot water from the tank making it safe for the

4 spray 120 mm optimised showerhead with rub-clean nozzles

Easy to clean smooth hose





Product Specification

Tech Details

Control type: Advanced pressure stabilised

Power options: 9.0 kW 240V AC (8.3 kW 230V AC);

9.8 kW 240V AC (9.0 kW 230V AC)

Supply voltage: $230V \pm 10\%$

Supply rating: 40 amp (9.0 kW); 45 amp (10.8 kW)

Terminal block connections: Maximum 16 mm²

Water entry points: Left (rising, falling & rear)

Cable entry points: Left (rising, falling & rear)

Inlet connections: Left: brass inlet connector. 15 mm compression fitting, Right: 15 mm plastic swivel stub compression or push fitting

Outlet connections: 1/2" BSP Male

Supply conditions

Minimum maintained pressure: 0.7 bar (7 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Temperature stability: ± 6°C

Phased shutdown: Yes

Factory set to safe max temp: No

Mira Sensi-flo™: Yes

Wide range of accessories available at www.mirashowers.co.uk

BEAB approved

Kiwa certified

WRAS approved

CE / UKCA marking











Dimensions



