

Mira Sport Multi-Fit™

Electric Shower



Experience long-lasting, powerful performance – from one of the UK's best-selling electric showers.

With a multi-fit design for easy replacement and a multi-mode showerhead for more spray experiences.

Product Information

Description	Colour	Product No.
Mira Sport Multi-Fit™ 9.0 kW	White/Chrome	1.1746.833
Mira Sport Multi-Fit™ 9.8 kW	White/Chrome	1.1746.834

Features & Benefits

Temperature control

Advanced pressure stabilised temperature control

Easy to fit

Retrofits onto inlets of most Mira, Triton, Bristan and Aquilisa electric showers

Adjustable slide bars fit over holes left by previous shower kit

Easy to service

Easy filter access

For your customer

Separate power and temperature controls

Push button on/off

Mira Sensi-flo™ technology helps prevent scalding

Mira Clearscale™ and Dual Element™ technology reduces limescale by up to 50%

Phased shutdown flushes hot water from the tank making it safe for the next user

4 spray 120 mm optimised showerhead with rub-clean nozzles

Easy to clean smooth hose



Product Specification

Tech Details

Temperature control

Control type: Advanced pressure stabilised

Installation

Power options: 9.0 kW 240V AC (8.3 kW 230V AC);
9.8 kW 240V AC (9.0 kW 230V AC)

Supply voltage: 230V ± 10%

Supply rating: 40 amp (9.0 kW); 45 amp (10.8 kW)

Terminal block connections: Maximum 16 mm²

Water entry points: Left (rising, falling & rear)

Cable entry points: Left (rising, falling & rear)

Inlet connections: Left: brass inlet connector. 15 mm compression fitting, Right: 15 mm plastic swivel stub compression or push fitting

Outlet connections: 1/2" BSP Male

Supply conditions

Minimum maintained pressure: 0.7 bar (7 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Temperature stability: ± 6°C

Safety Features

Phased shutdown: Yes

Factory set to safe max temp: No

Mira Sensi-flo™: Yes

Accessories

Wide range of accessories available at www.mirashowers.co.uk

Approvals

BEAB approved

Kiwa certified

WRAS approved

CE / UKCA marking



Dimensions

