

Features

- Solid metal construction.
- Leak-free ceramic disc valve with lifetime warranty.
- Durable KOHLER finishes resist corrosion and tarnishing.
- Coin aerator allows for easy cleaning and maintenance.
- 120 mm spout reach (K-29176T-4).
- 130 mm spout reach (K-29547T-4).
- Includes pop-up drain (K-29176T-4).
- Includes click drain (K-29547T-4).

Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB 18145-2014
- TIS 2067-2552

Installation Notes

Install this product according to the installation guide.


SINGLE HANDLE LAVATORY FAUCET K-29176T-4 / K29547T-4




Specified Model

Model	Description	Color/Finishes	
K-29176T-4	Fore Arc single handle lavatory faucet	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-29547T-4	Fore Arc single handle tall lavatory faucet	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others

For a full range of color finishes in your market please contact your local Kohler representative.





Flow Curve
K-29176T-4



Flow Curve
K-29547T-4

Note: Flow rates are approximate. (1 gallon = 3.758 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากโลหะ
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษจากโคห์โลร์ คงทน เงางาม
- ปากก๊อกแบบเหรียญช่วยให้ทำความสะอาดและบำรุงรักษาได้ง่าย
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 120 มม. (K-29176T-4)
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 130 มม. (K-29547T-4)
- พร้อมสะดืออ่างแบบป๊อปอัพ (K-29176T-4)
- พร้อมสะดืออ่างแบบกด (K-29547T-4)

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- GB 18145-2014
- มอก. 2067-2552


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-29176T-4	ก๊อกผสมอ่างล้างหน้าแบบก้านโยก รุ่นฟอร์ อาร์ค	<input type="checkbox"/> CP: สีโครมเงา	<input type="checkbox"/> สีอื่นๆ
K-29547T-4	ก๊อกผสมอ่างล้างหน้าทรงสูงแบบก้านโยก รุ่นฟอร์ อาร์ค	<input type="checkbox"/> CP: สีโครมเงา	<input type="checkbox"/> สีอื่นๆ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์โลร์ในประเทศของท่าน





K-29176T-4



K-29547T-4

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง
ภาพแสดงผลผลิตภัณฑ์