

Features

- Brass construction.
- Leak-free ceramic disc valve with lifetime warranty.
- Durable Kohler finishes resist corrosion and tarnishing.
- Coin aerator allows for easy cleaning and maintenance.
- Lever handle (K-34310X-4).
- Upright handle (K-34313X-4).
- 110 mm spout reach.
- Includes pop-up drain.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB 18145-2014
- TIS 2067-2552

Installation Notes

Install this product according to the installation guide.


SINGLE-HOLE LAVATORY FAUCET
K-34310X-4/K-34313X-4



Specified Model

Model	Description	Colors/Finishes
K-34310X-4	Atom single-hole lavatory faucet	CP: Polish chrome
K-34313X-4	Atom single-hole lavatory faucet	CP: Polish chrome


For a full range of color finishes in your market please contact your local Kohler representative.




Note: Flow rates are approximate. (1 gallon = 3.758 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)

Unit: mm



K-34310X-4



K-34313X-4

Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษของโคห์เลอร์ คงทน งาม
- ปากก๊อกง่ายต่อการทำความสะอาดและบำรุงรักษา
- มือบิดก้านโยก (K-34310X-4)
- มือบิดแบบ Upright (K-34313X-4)
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 110 มม.
- พร้อมสวิตช์อ่างล้างหน้าแบบป๊อปอัพ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- GB 18145-2014
- มอก. 2067-2552

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


ก๊อกผสมอ่างล้างหน้าแบบก้านโยก K-34310X-4/K-34313X-4



รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-34310X-4	ก๊อกผสมอ่างล้างหน้าแบบก้านโยก รุ่นอะตอม	CP: สีโครมเงา
K-34313X-4	ก๊อกผสมอ่างล้างหน้าแบบก้านโยก รุ่นอะตอม	CP: สีโครมเงา

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์ จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศไทยของท่าน




หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.758 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.



K-34310X-4



K-34313X-4

หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง
ภาพแสดงผลิตภัณฑ์