

Features


- Vitreous china.
- Elongated bowl.
- Includes quiet close seat.
- Includes polished chrome push button.
- Class Five+ dual flush system.
- 3/4.8 liter per flush.
- 305 mm rough-in for S-trap.
- 730 x 370 x 805 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1

TWO-PIECE TOILET WITH SEAT K-5331K



Technical Information

Fixture:	
Configuration	two-piece, elongated
Water per flush	3/4.8 liter
Passageway	51 mm
Water area	255 x 185 mm
Water depth from rim	165 mm
Seat post hole centers	140 mm

Included Components:	
Bowl	K-5773K-**
Tank	K-5776T-**
Tank cover	1205663-SP-**
Quiet close seat	K-4141T-2P-**

Installation Notes

Install this product according to the installation guide.

Specified Model


Model	Description	Color/Finishes
K-5331K-S	Karess two-piece toilet, S-trap with quiet close seat	0: White

Recommended Accessories		
1548548-SP	Water Supply Hose, Stainless	N/A
1552115-SP	Shut Off Valve	CP: Polished Chrome


Dimensions are approximate. (Do not direct measure a dimensional from picture below.)

Unit: mm

This diagram shown with K-4141T-2P seat



For plastic connector installation



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.
Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

Product Diagram